



A-Shape LED

EcoHome LEDBulb 4W E27 6500K A60 1PF AR

LEDbulb, A60, 40 W, E27, 6500 K, 350 lm, 10000 hour(s), Plastic

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	10,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Warranty period	1 years
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	350 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	4 W
Lamp Current (Nom)	36 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60
Net Weight (Piece)	0.026 kg

A-Shape LED

Approval and Application

EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	EcoHome LEDBulb 4W E27 6500K A60 1PF AR
Full product name	EcoHome LEDBulb 4W E27 6500K A60 1PF AR



Full product code	872016920552900
Order code	929003652071
Material Nr. (12NC)	929003652071
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169205529
Numerator - Packs per outer box	20
EAN/UPC - Case	8720169205536

Dimensional drawing



Product	D	C
EcoHome LEDBulb 4W E27 6500K A60 1PF AR	60 mm	107 mm

Photometric data




General uniform lighting - EcoHome LEDBulb 4W E27 6500K A60 1PF AR

Light Distribution Diagram - EcoHome LEDBulb 4W E27 6500K A60 1PF AR


A-Shape LED

Photometric data




Spectral Power Distribution Colour - EcoHome LEDBulb 4W E27 6500K A60 1PF AR

Lifetime



Lumen Maintenance Diagram - EcoHome LEDBulb 4W E27 6500K A60 1PF AR



Life Expectancy Diagram

