



Contractor-grade Plastic (Dimmable) A-Shape Lamps

5A19/CNG/840/FR/P/E26/D 12/1CT

Contractor grade, LEDbulb, A19, 40 W, E26, 4000 K, 450 lm, 15000 hour(s), Plastic

Plastic A19 offering dimmability and a lifetime over 15,000 hours. Ideal for contractor-grade residential and multi-family spaces.

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	450 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	90 °C

Contractor-grade Plastic (Dimmable) A-Shape Lamps

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.026 kg

Approval and Application

EU RoHS compliant	Yes
T20 compliant	No
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	5A19/CNG/840/FR/P/E26/D 12/1CT
Full product name	5A19/CNG/840/FR/P/E26/D 12/1CT
Order code	929003751164
Material Nr. (12NC)	929003751164
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677589622
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677589627

Dimensional drawing



Product	D	C
5A19/CNG/840/FR/P/E26/D 12/1CT	60 mm	104 mm

Photometric data




Spectral Power Distribution Colour - 5A19/CNG/840/FR/P/E26/D 12/1CT

General uniform lighting - 5A19/CNG/840/FR/P/E26/D 12/1CT

Contractor-grade Plastic (Dimmable) A-Shape Lamps

Photometric data



Light Distribution Diagram - 5A19/CNG/840/FR/P/E26/D 12/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5A19/CNG/840/FR/P/E26/D 12/1CT

