



MyCare LED Circular

LED MOD 25W G3 865

LEDtube, Others, Mains, 200 mm, 25 W, 6500 K, 2400 lm, 20000 hour(s)

LEDtube, Others, Mains, 200 mm, 25 W, 6500 K, 2400 lm, 20000 hour(s), 96 lm/W, Plastic, RG1

Product data

General Information			
Cap-Base	-	Lamp Current (Nom)	180 mA
Nominal lifetime	20,000 hour(s)	Wattage Equivalent	40 W
Switching Cycle	15,000	Starting Time (Nom)	0.5 s
Lighting Technology	LEDtube	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
		Ballast Compatibility	Mains
Light Technical		Temperature	
Color Code	865 [CCT of 6500K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	150 degree(s)		
Luminous Flux	2,400 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	96 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	83	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	200 mm
Photobiological safety according to EN 62471	RG1	Overall length	21.5 mm
		Overall width	155 mm
		Overall height	21.5 mm
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power Consumption	25 W		

MyCare LED Circular

Dimensions (Height x Width x Depth)	22 x 155 x 22 mm
Bulb Shape	Others
Net Weight (Piece)	0.105 kg

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LED MOD 25W G3 865
Full product name	LED MOD 25W G3 865
Full product code	694197061200500
Order code	929003765909
Material Nr. (12NC)	929003765909
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6941970612005
Numerator - Packs per outer box	40
EAN/UPC - Case	6941970612012

Dimensional drawing



Product	D1	D2	A1	A2	A3
LED MOD 25W G3 865	178.5 mm	178.5 mm	21 mm	160 mm	178.5 mm


Photometric data



General uniform lighting - LED MOD 25W G3 865


Spectral Power Distribution Colour - LED MOD 25W G3 865

Photometric data




Light Distribution Diagram - LED MOD 25W G3 865


Lifetime




FailureRate



Life Expectancy Diagram




Lumen Maintenance Diagram - LED MOD 25W G3 865



Lumen Maintenance Diagram - LED MOD 25W G3 865

MyCare LED Circular

Lifetime



LifetimeVsTc

