



# Dipswitch LED bulb

## LEDStick 10W E27 DS FR DIM 1PF/6 AU

LEDbulb, Stick, 75 W, E27, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 1000 lm, 15000 hour(s), Plastic

Not sure about the color that will best fit your application? No need to worry. Philips Dipswitch LED bulb offer 5 colors in one product and is easy-to-operate by switching the button to change the color.

### Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	2700K/3000K/4000K/5000K/6500K
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,000 lm
Color Designation	2700K/3000K/4000K/5000K/6500K
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W

Lamp Current (Nom)	45 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	107 mm
Overall width	41 mm
Overall height	107 mm
Dimensions (Height x Width x Depth)	107 x 41 x 107 mm

# Dipswitch LED bulb

Bulb Shape	Stick
Net Weight (Piece)	0.048 kg

## Approval and Application

EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


## Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

## Product Data


Order product name	LEDStick 10W E27 DS FR DIM 1PF/6 AU
Full product name	LEDStick 10W E27 DS FR DIM 1PF/6 AU
Full product code	872016930081100
Order code	929003785619
Material Nr. (12NC)	929003785619
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300811
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300828

## Dimensional drawing




Product	D	C
LEDStick 10W E27 DS FR DIM 1PF/6 AU	41 mm	107 mm

## Photometric data



Spectral Power Distribution Colour - LEDStick 10W E27 DS FR DIM 1PF/6 AU



Light Distribution Diagram - LEDStick 10W E27 DS FR DIM 1PF/6 AU

