



Multi-CCT Dimmable LED bulbs

LEDStick 10W E27 DS FR DIM 1PF/6 AU

LEDbulb, Stick, 75 W, E27, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 1000 lm, 15000 h, Plastic

LEDbulb, Stick, 75 W, E27, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 1000 lm, 15000 h, Plastic, 100 lm/W

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	2700K/3000K/4000K/5000K/6500K
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,000 lm
Color Designation	2700K/3000K/4000K/5000K/6500K
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	10 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	107 mm
Overall width	41 mm

Multi-CCT Dimmable LED bulbs

Overall height	107 mm
Dimensions (Height x Width x Depth)	107 x 41 x 107 mm
Bulb Shape	Stick
Net Weight (Piece)	0.048 kg

Approval and Application

EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LEDStick 10W E27 DS FR DIM 1PF/6 AU
Full product name	LEDStick 10W E27 DS FR DIM 1PF/6 AU
Full product code	872016930081100
Order code	929003785619
Material Nr. (12NC)	929003785619
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300811
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300828

Dimensional drawing



Product	D	C
LEDStick 10W E27 DS FR DIM 1PF/6 AU	41 mm	107 mm

Photometric data



Spectral Power Distribution Colour - LEDStick 10W E27 DS FR DIM 1PF/6 AU

Light Distribution Diagram - LEDStick 10W E27 DS FR DIM 1PF/6 AU

