



Multi-CCT Dimmable LED bulbs

LEDStick 14W B22 DS FR DIM 1PF/6 AU

LEDbulb, Stick, 100 W, B22, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 1400 lm, 15000 h, Plastic

LEDbulb, Stick, 100 W, B22, 2700 K, 3000 K, 4000 K, 5000 K, 6500 K, 1400 lm, 15000 h, Plastic, 100 lm/W

Product data

General Information		Power Consumption	
Cap-Base	B22	Lamp Current (Nom)	60 mA
Nominal lifetime	15,000 h	Wattage Equivalent	100 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LEDbulb	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	2700K/3000K/4000K/5000K/6500K	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	200 degree(s)		
Luminous Flux	1,400 lm	Controls and Dimming	
Color Designation	2700K/3000K/4000K/5000K/6500K	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	2700 3000 4000 5000 6500 K		
Luminous Efficacy (rated) (Nom)	100 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Overall length	132 mm
		Overall width	41 mm
Operating and Electrical			
Input Frequency	50 to 60 Hz		

Multi-CCT Dimmable LED bulbs

Overall height	132 mm
Dimensions (Height x Width x Depth)	132 x 41 x 132 mm
Bulb Shape	Stick
Net Weight (Piece)	0.063 kg

Approval and Application

EU RoHS compliant	Yes
Warranty	2 year(s)
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	LEDStick 14W B22 DS FR DIM 1PF/6 AU
Full product name	LEDStick 14W B22 DS FR DIM 1PF/6 AU
Full product code	872016930087300
Order code	929003785919
Material Nr. (12NC)	929003785919
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169300873
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169300880

Dimensional drawing



Product	D	C
LEDStick 14W B22 DS FR DIM 1PF/6 AU	41 mm	132 mm

Photometric data




Spectral Power Distribution Colour - LEDStick 14W B22 DS FR DIM 1PF/6 AU

General uniform lighting - LEDStick 14W B22 DS FR DIM 1PF/6 AU

Multi-CCT Dimmable LED bulbs

Photometric data



Light Distribution Diagram - LEDStick 14W B22 DS FR DIM 1PF/6 AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDStick 14W B22 DS FR DIM 1PF/6 AU

