



# A-Shape LED

## LEDBulb 11W E27 3000K W A19 1PF/6

LEDBulb, A19, 75 W, E27, 3000 K, 910 lm, 15000 hour(s), Plastic

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	E27		140 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	75 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LEDBulb	Warm-up time to 60% light	0.5 s
Warranty period	1 years	Power Factor (Fraction)	0.5
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	150 degree(s)		
Luminous Flux	910 lm	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	82 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A19
		Net Weight (Piece)	0.026 kg
Operating and Electrical		Approval and Application	
Input Frequency	60 Hz	EU RoHS compliant	Yes
Power Consumption	11 W		

# A-Shape LED

Ambient temperature range	-20 to +45 °C
<b>Application Conditions</b>	
Wireless Technology	Not applicable
<b>Product Data</b>	
Order product name	LEDBulb 11W E27 3000K W A19 1PF/6
Full product name	LEDBulb 11W E27 3000K W A19 1PF/6
Full product code	871869970287801



Order code	929003797713
Material Nr. (12NC)	929003797713
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699702878
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169309791

## Dimensional drawing




Product	D	C
LEDBulb 11W E27 3000K W A19 1PF/6	60 mm	109 mm

## Photometric data



Light Distribution Diagram - LEDBulb 11W E27 3000K W A19 1PF/6



General uniform lighting - LEDBulb 11W E27 3000K W A19 1PF/6



Spectral Power Distribution Colour - LEDBulb 11W E27 3000K W A19 1PF/6

# A-Shape LED

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 11W E27 3000K W A19 1PF/6

