



MASTER LEDtube T8

MAS LEDtube 600mm HO 8W840 T8

MASTER, LEDtube, T8, EM/Mains, Single-end, 600 mm, 220-240 V, 8 W, 18W TL-D, 4000 K, 1200 lm, 60000 hour(s)

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

-
-

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom)		70 %
Cap-Base	G13	Photobiological safety according to EN 62471		RG0
Nominal lifetime	60,000 hour(s)	Operating and Electrical		
Switching Cycle	200,000	Input Frequency	50 to 60 Hz	
Lighting Technology	LEDtube	Power Consumption	8 W	
Light Technical		Lamp Current (Max)	40 mA	
Color Code	840 [CCT of 4000K]	Lamp Current (Min)	37 mA	
Beam Angle (Nom)	190 degree(s)	Wattage Equivalent	18 W	
Luminous Flux	1,200 lm	Starting Time (Nom)	0.5 s	
Color Designation	Cool White (CW)	Warm-up time to 60% light	0.5 s	
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	0.9	
Luminous Efficacy (rated) (Nom)	150 lm/W	Voltage (Nom)	220-240 V	
Color Consistency	<6	LED alternative to fluorescent lamp power	18W TL-D	
Color rendering index (CRI)	80			

MASTER LEDtube T8

Ballast Compatibility	EM/Mains
Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	600 mm
Bulb Shape	T8
Net Weight (Piece)	0.090 kg
Approval and Application	
Energy Saving Product	Yes



Approval Marks	RoHS compliance KEMA Keur certificate
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	MAS LEDtube 600mm HO 8W840 T8
Full product name	MAS LEDtube 600mm HO 8W840 T8
Full product code	872016931593800
Order code	929003805808
Material Nr. (12NC)	929003805808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169315938
Numerator - Packs per outer box	20
EAN/UPC - Case	8720169315945

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 600mm HO 8W840 T8	25.8 mm	28 mm	595.7 mm	598.8 mm	604 mm

Photometric data




General uniform lighting - MAS LEDtube 600mm HO 8W840 T8

Spectral Power Distribution Colour - MAS LEDtube 600mm HO 8W840 T8


MASTER LEDtube T8

Photometric data




Light Distribution Diagram - MAS LEDtube 600mm HO 8W840 T8


Lifetime




Lumen Maintenance Diagram - MAS LEDtube 600mm HO 8W840 T8



LEDtube 60K 5070 LifetimeVsTc-LED




Lumen Maintenance Diagram - MAS LEDtube 600mm HO 8W840 T8



Life Expectancy Diagram

MASTER LEDtube T8

Lifetime



LEDtube 60K 5070 FailureRate-LED

