



中国国家强制性产品认证证书

证书编号: 2024011002613608

认证委托人名称及地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞(中国)投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交流电子控制装置(LED 控制装置, 内装式, 恒流模式, 自耦式, 不可调光, $t_c: 85^{\circ}\text{C}$, 定温热保护: 110°C)
见附页。220-240V~ 50/60Hz

产品标准和技术要求

GB 17625.1-2022; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合《强制性产品认证实施规则 照明电器》(CNCA-C10-01:2014)的要求, 特发此证。

发证日期: 2024 年 10 月 22 日 有效期至: 2029 年 03 月 14 日

本证书为变更证书, 证书首次颁发日期: 2024 年 03 月 15 日
证书信息和有效性可扫描下方二维码或登录发证机构网站查验,
也可在认监委网站(www.cnca.gov.cn)查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024011002613608

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China.

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China.

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Constant Current Mode,
Auto-wound Controlgear, Non-dimmable, tc:85°C, Temperature Declared Thermally Protected:110°C)
See Appendix. 220-240V ~ 50/60Hz

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Oct.22,2024

Valid until: Mar.14,2029

Date of original issued: Mar.15,2024

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





中国国家强制性产品认证证书

证书编号: 2024011002613608

证书附页: 第 1 页 共 1 页

序号	产品型号	参数	拨码开关																				
1.	Xitanium 150W 400-700mA 215V DS 230V	输入 : 220-240V ~ , 50/60Hz, 0.75A, λ : 0.9C; 输出 : 140-215V =, Max 300V=, 恒流	<table><tr><th>Prated</th><th>Irated</th><th>Pin1</th><th>Pin2</th></tr><tr><td>86W</td><td>0.40A</td><td>ON</td><td>ON</td></tr><tr><td>107.5W</td><td>0.50A</td><td>ON</td><td>OFF</td></tr><tr><td>129W</td><td>0.60A</td><td>OFF</td><td>ON</td></tr><tr><td>150W</td><td>0.70A</td><td>OFF</td><td>OFF</td></tr></table>	Prated	Irated	Pin1	Pin2	86W	0.40A	ON	ON	107.5W	0.50A	ON	OFF	129W	0.60A	OFF	ON	150W	0.70A	OFF	OFF
Prated	Irated	Pin1	Pin2																				
86W	0.40A	ON	ON																				
107.5W	0.50A	ON	OFF																				
129W	0.60A	OFF	ON																				
150W	0.70A	OFF	OFF																				
2.	Xitanium 100W 350-500mA 200V DS 230V	输入 : 220-240V ~ , 50/60Hz, 0.5A, λ : 0.9C; 输出 : 100-200V =, Max 250V=, 恒流	<table><tr><th>Prated</th><th>Irated</th><th>Pin1</th><th>Pin2</th></tr><tr><td>70W</td><td>0.35A</td><td>ON</td><td>ON</td></tr><tr><td>80W</td><td>0.40A</td><td>ON</td><td>OFF</td></tr><tr><td>90W</td><td>0.45A</td><td>OFF</td><td>ON</td></tr><tr><td>100W</td><td>0.50A</td><td>OFF</td><td>OFF</td></tr></table>	Prated	Irated	Pin1	Pin2	70W	0.35A	ON	ON	80W	0.40A	ON	OFF	90W	0.45A	OFF	ON	100W	0.50A	OFF	OFF
Prated	Irated	Pin1	Pin2																				
70W	0.35A	ON	ON																				
80W	0.40A	ON	OFF																				
90W	0.45A	OFF	ON																				
100W	0.50A	OFF	OFF																				
3.	Xitanium 80W 400-550mA 200V DS 230V	输入 : 220-240V ~ , 50/60Hz, 0.39A, λ : 0.9C; 输出 : 80-200V=, Max 250V=, 恒流	<table><tr><th>Prated</th><th>Irated</th><th>Pin1</th><th>Pin2</th></tr><tr><td>80W</td><td>0.40A</td><td>ON</td><td>ON</td></tr><tr><td>80W</td><td>0.45A</td><td>ON</td><td>OFF</td></tr><tr><td>80W</td><td>0.50A</td><td>OFF</td><td>ON</td></tr><tr><td>80W</td><td>0.55A</td><td>OFF</td><td>OFF</td></tr></table>	Prated	Irated	Pin1	Pin2	80W	0.40A	ON	ON	80W	0.45A	ON	OFF	80W	0.50A	OFF	ON	80W	0.55A	OFF	OFF
Prated	Irated	Pin1	Pin2																				
80W	0.40A	ON	ON																				
80W	0.45A	ON	OFF																				
80W	0.50A	OFF	ON																				
80W	0.55A	OFF	OFF																				
tc: 85°C,  , 自耦式, 内装式																							

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司