EU Declaration of Conformity

Document No.: 2026A0070
Year in which CE Mark was first affixed: 2023

1. Product Range / Model:

Product Range / Model:	**NAME:** Electronic Controlgear for LED modules **DESCRIPTION**: Xi Track 3C LED Drivers including packaging **BRAND**: PHILIPS or XITANIUM or SIGNIFY

2. Manufacturer Name & Address:

Signify
I.B.R.S./C.C.R.I. /Numéro 10461
5600 VB Eindhoven, The Netherlands

3. This declaration of conformity is issued under the sole responsibility of the manufacturer.

4. Object of the declaration:

Product Code:	Unique product ID number of all products under the family described above, please refer to the Annex: Specification of the products.

5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Low Voltage Directive (LVD), 2014/35/EU

- EN 61347-1 : 2015+A1 :2021
- EN 61347-2-13 :2014 + A1 :2017
- EN 62493:2015+A1:2022

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN IEC 55015: 2019 + A11: 2020
- EN IEC 61000-3-2 : 2019 + A1 : 2021 + A2 :2024
- EN 61000-3-3 : 2013 + A1 : 2019 + A2 : 2021 + AC :2022
- EN IEC 61547: 2023

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- Commission Regulation (EU) 2019/2020 and amendment Commission Regulation (EU) 2021/341

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU and applicable Delegated Directives

- EN IEC 63000:2018

Packaging and Packaging Waste Regulation (PPWR), (EU) 2025/40

7. Additional information: The product(s) in this declaration is/are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Signed for and on behalf of:

SIGNIFY
I.B.R.S/C.C.R.I/Numéro 10461
5600 VB Eindhoven
The Netherlands

2026-06-30, Eindhoven
Hans Bellemans
Head of Quality OEM

EU Declaration of Conformity

Document No.: 2026A0070

Specification of the products:

10NC	12NC	Product Description	Brand	Remarks
9290028498	929002849880	Xi 34W/a 0.7-0.85A 40V DS 3CW 230V	PHILIPS or XITANIUM	N/A
9290028499	929002849980	Xi 34W/a 0.7-0.85A 40V DS 3CB 230V	PHILIPS or XITANIUM	N/A
9290028500	929002850080	Xi 34W/a 0.7-0.85A 40V DS 3CG 230V	PHILIPS or XITANIUM	N/A
9290028501	929002850180	Xi 42W/a 0.9-1.05A 40V DS 3CW 230V	PHILIPS or XITANIUM	N/A
9290028502	929002850280	Xi 42W/a 0.9-1.05A 40V DS 3CB 230V	PHILIPS or XITANIUM	N/A
9290028503	929002850380	Xi 42W/a 0.9-1.05A 40V DS 3CG 230V	PHILIPS or XITANIUM	N/A
9290034257	929003425706	Xitanium 42W/a 0.3-1.05A 48V TD 3CW	PHILIPS or XITANIUM	N/A
9290034258	929003425806	Xitanium 42W/a 0.3-1.05A 48V TD 3CB	PHILIPS or XITANIUM	N/A
9290034259	929003425906	Xitanium 42W/a 0.3-1.05A 48V TD 3CG	PHILIPS or XITANIUM	N/A
9290034508	929003450806	Xi 14W/a 0.2-0.35A 40V DS 3CW 230V	PHILIPS or XITANIUM	N/A
9290034509	929003450906	Xi 14W/a 0.2-0.35A 40V DS 3CB 230V	PHILIPS or XITANIUM	N/A
9290034510	929003451006	Xi 14W/a 0.2-0.35A 40V DS 3CG 230V	PHILIPS or XITANIUM	N/A
9290034511	929003451106	Xi 26W/a 0.5-0.65A 40V DS 3CW 230V	PHILIPS or XITANIUM	N/A
9290034512	929003451206	Xi 26W/a 0.5-0.65A 40V DS 3CB 230V	PHILIPS or XITANIUM	N/A
9290034513	929003451306	Xi 26W/a 0.5-0.65A 40V DS 3CG 230V	PHILIPS or XITANIUM	N/A
9290038655	929003865580	Xi 34W/a 0.7-0.85A 40V DS 3CW 230V	PHILIPS or XITANIUM	N/A
9290038656	929003865680	Xi 34W/a 0.7-0.85A 40V DS 3CB 230V	PHILIPS or XITANIUM	N/A
9290038657	929003865780	Xi 34W/a 0.7-0.85A 40V DS 3CG 230V	PHILIPS or XITANIUM	N/A
9290038658	929003865880	Xi 42W/a 0.9-1.05A 40V DS 3CW 230V	PHILIPS or XITANIUM	N/A
9290038659	929003865980	Xi 42W/a 0.9-1.05A 40V DS 3CB 230V	PHILIPS or XITANIUM	N/A
9290038660	929003866080	Xi 42W/a 0.9-1.05A 40V DS 3CG 230V	PHILIPS or XITANIUM	N/A
9290039214	929003921406	Xitanium 12W 0.15-0.3A 40V HE 3CW 230V	PHILIPS or XITANIUM	N/A
9290039215	929003921506	Xitanium 12W 0.15-0.3A 40V HE 3CB 230V	PHILIPS or XITANIUM	N/A
9290039216	929003921606	Xitanium 12W 0.15-0.3A 40V HE 3CG 230V	PHILIPS or XITANIUM	N/A
9290039217	929003921706	Xitanium 28W 0.35-0.7A 40V HE 3CW 230V	PHILIPS or XITANIUM	N/A
9290039218	929003921806	Xitanium 28W 0.35-0.7A 40V HE 3CB 230V	PHILIPS or XITANIUM	N/A
9290039219	929003921906	Xitanium 28W 0.35-0.7A 40V HE 3CG 230V	PHILIPS or XITANIUM	N/A
9290039220	929003922006	Xitanium 42W 0.7-1.05A 40V HE 3CW 230V	PHILIPS or XITANIUM	N/A
9290039221	929003922106	Xitanium 42W 0.7-1.05A 40V HE 3CB 230V	PHILIPS or XITANIUM	N/A
9290039222	929003922206	Xitanium 42W 0.7-1.05A 40V HE 3CG 230V	PHILIPS or XITANIUM	N/A
9290048706	929004870601	Xi 18W/a 0.3-0.45A 40V DS 3CW 230V UHE	PHILIPS or SIGNIFY	N/A
9290048707	929004870701	Xi 18W/a 0.3-0.45A 40V DS 3CB 230V UHE	PHILIPS or SIGNIFY	N/A
9290048708	929004870801	Xi 18W/a 0.3-0.45A 40V DS 3CG 230V UHE	PHILIPS or SIGNIFY	N/A
9290048709	929004870901	Xi 26W/a 0.5-0.65A 40V DS 3CW 230V UHE	PHILIPS or SIGNIFY	N/A
9290048710	929004871001	Xi 26W/a 0.5-0.65A 40V DS 3CB 230V UHE	PHILIPS or SIGNIFY	N/A
9290048711	929004871101	Xi 26W/a 0.5-0.65A 40V DS 3CG 230V UHE	PHILIPS or SIGNIFY	N/A
9290048838	929004883801	Xi 15W/a 0.375A 40V SC 3CW 230V UHE	PHILIPS or SIGNIFY	N/A
9290048839	929004883901	Xi 15W/a 0.375A 40V SC 3CB 230V UHE	PHILIPS or SIGNIFY	N/A
9290048846	929004884601	Xi 15W/a 0.375A 40V SC 3CG 230V UHE	PHILIPS or SIGNIFY	N/A