产品认证证书

灯具用电源导轨系统安全与电磁兼容认证

证书编号：CQC25010458102

发证日期：2026 年 06 月 10 日
有效期至：2030 年 01 月 07 日

委托人名称及注册地址	昕诺飞（中国）投资有限公司 上海市闵行区田林路 888 弄 9 号楼
制造商名称及注册地址	昕诺飞（中国）投资有限公司 上海市闵行区田林路 888 弄 9 号楼
生产企业名称及生产地址	
产品名称和系列、规格、型号	灯具用电源导轨系统（导轨接合器（Ⅱ类），集成 LED 模块用交流电子控制装置，ta：35℃，tc：80℃，安全特低电压，适宜直接安装在普通可燃材料表面） 见附页。220-240V～ 50/60Hz
产品标准和技术要求	GB 17625.1-2022;GB/T 17743-2021;IEC 60570 : 2019;GB/T 7000.1-2023
认证模式	产品型式试验+初始工厂检查+获证后监督

上述产品符合 CQC12-465431-2026 认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2025 年 01 月 08 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

签发：

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司 1101061026946

中国质量认证中心有限公司
中国·北京·南四环西路188号9区 100070
电话：+86 10 83886666
http://www.cqc.com.cn

CERTIFICATE OF PRODUCT CERTIFICATION

SAFETY AND ELECTROMAGNETIC COMPATIBILITY CERTIFICATION FOR ELECTRICAL SUPPLY TRACK SYSTEMS FOR LUMINAIRES

CERTIFICATE NO.: CQC25010458102

Valid from: Jun.10,2026

Valid until:Jan.07,2030

NAME AND REGISTERED ADDRESS OF THE APPLICANT	Signify (China) Investment Co., Ltd. Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	Signify (China) Investment Co., Ltd. Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China
NAME AND LOCATION OF THE FACTORY	
PRODUCT NAME, MODEL AND SPECIFICATION	Electrical Supply Track System For Luminaires (Adaptor（ClassⅡ）, Integrated A.C. Supplied Electronic Controlgear For LED Modules, ta：35℃, tc：80℃, SELV, Suitable For Direct Mounting On Normally Flammable Material Surfaces) See Appendix. 220-240V～ 50/60Hz
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB 17625.1-2022;GB/T 17743-2021;IEC 60570 : 2019;GB/T 7000.1-2023
TYPE OF CERTIFICATION SCHEMES	Product Type Testing + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-465431-2026.

Date of original issued: Jan.08,2025

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGNATURE:

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司 1101061026946

产品认证证书

证书编号：CQC25010458102　　第 1 页 /共 1 页

本证书及附件应同时使用，信息查验说明见证书页　　纸号：

XITANIUM 42W 0.7-1.05A 40V HE 3CB 230V,
XITANIUM 42W 0.7-1.05A 40V HE 3CG 230V,
XITANIUM 42W 0.7-1.05A 40V HE 3CW 230V,
XITANIUM 28W 0.35-0.7A 40V HE 3CB 230V,
XITANIUM 28W 0.35-0.7A 40V HE 3CG 230V,
XITANIUM 28W 0.35-0.7A 40V HE 3CW 230V,
XITANIUM 12W 0.15-0.3A 40V HE 3CB 230V,
XITANIUM 12W 0.15-0.3A 40V HE 3CG 230V,
XITANIUM 12W 0.15-0.3A 40V HE 3CW 230V,
以上均为：220-240V～ 50/60Hz Fmax：50N，Uout：60VdcMAX。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司
中国·北京·南四环西路188号9区 100070
电话：+86 10 83886666
http://www.cqc.com.cn