Australia and New Zealand Certificate of Suitability- addendum

Certificate
ULL-103670-A1

Issue date
2026-06-05

Expiration date
2029-11-25

This is to acknowledge that

Signify Netherlands B.V.

High Tech Campus 48, EINDHOVEN 5656 AE
Netherlands

has had

Electronic Controlgear for LED modules {component for building in}

[refer following page(s) for models list]

evaluated and meets the requirements of the standard(s)

AS 61347.2.13:2018; AS/NZS 61347.1:2016, Amd 1: 2018, Amd 2: 2025

ANZ Certification Scheme requirements.

Amarjit Singh (Certification Officer)

Certification Body:
UL International New Zealand Limited,
54 Tarndale Grove, Albany, Auckland 0632, New Zealand.

Issued for use in Australia and New Zealand only.
All dates are in Year-Month-Day format (YYYY-MM-DD).

JAS-ANZ

www.jasanz.org/register

UL Solutions

© 2026 UL LLC. All rights reserved.

Australia and New Zealand
Certificate of Suitability-addendum

Certificate No: ULL-103670-A1
Original Date of Certification: 2024-11-25
Date of Issue/Revision: 2026-06-05

Trade Name or Trademark: PHILIPS, SIGNIFY, XITANIUM, ADVANCE

Risk Class / NSW Declared Class: EESS OUT OF SCOPE - Non-prescribed / non-declared

IEC Standard Country Differences: AU and NZ

Certification Marking: The RCM may be applied to the product and all the requirements of all relevant parts of AS/NZS 4417 applicable to the article shall be fulfilled.

Additional Certification Conditions: None.

Model Details and Rating:

Product data – type Xitanium 25W 0.03-0.3A 220V TD16 230V
Ratings: Uin: 220-240 Vac, Iin: 0.12 Aac, Pin: 28 W,
Uin:186-250 Vdc, Iin: 0.11-0.15 Adc,
fn: 50/60 Hz, DC, PF: 0.9C,
Prated: 25 W, Irated: 0.035-0.3 Adc,
Output voltage range: 50-220 Vdc, Uout: 250 V,
ta: -25…+50 °C, tc: 80 °C, built-in, output not mains isolated.

Product data – type Xitanium 35W 0.08-0.35A 220V TD16 230V
Ratings: Uin: 220-240 Vac, Iin: 0.18 Aac, Pin: 39 W,
Uin:186-250 Vdc, Iin: 0.15-0.2 Adc,
fn: 50/60 Hz, DC, PF: 0.9C,
Prated: 35 W, Irated: 0.08-0.35 Adc,
Output voltage range: 50-220 Vdc, Uout: 250 V,
ta: -25…+50 °C, tc: 80 °C, built-in, output not mains isolated.

Product data – type Xitanium 60W 0.08-0.35A 300V TD16 230V
Ratings: Uin: 220-240 Vac, Iin: 0.3 Aac, Pin: 66 W,
Uin:186-250 Vdc, Iin: 0.26-0.35 Adc,
fn: 50/60 Hz, DC, PF: 0.9C,
Prated: 60 W, Irated: 0.08-0.35 Adc,
Output voltage range: 100-300 Vdc, Uout: 330 V,
ta: -25…+50 °C, tc: 80 °C, built-in, output not mains isolated.

Product data – type Xitanium 60W 0.15-0.5A 220V TD16 230V
Ratings: Uin: 220-240 Vac, Iin: 0.3 Aac, Pin: 66 W,
Uin:186-250 Vdc, Iin: 0.26-0.35 Adc,
fn: 50/60 Hz, DC, PF: 0.9C,
Prated: 60 W, Irated: 0.15-0.5 Adc,
Output voltage range: 50-220 Vdc, Uout: 250 V,
ta: -25…+50 °C, tc: 80 °C, built-in, output not mains isolated.

Details of addendum :
Trade names “XITANIUM”, and “ADVANCE” added.

© 2026 UL LLC. All rights reserved.