



# 中国国家强制性产品认证证书

证书编号：2025011002755791

认证委托人名称及地址

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产者名称及地址

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, 荷兰

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交直流电子控制装置 (LED 控制装置, 内装式, 自耦式, 恒流模式, ta:  
60°C, tc: 90°C, EL, 定温热保护: 110°C, 控制端口调光)  
见附页。220-240V~ 50/60Hz, 186-250Vdc

产品标准和技术要求

GB 17625.1-2022; GB/T 17743-2021; GB/T 19510.1-2023; GB/T 19510.213-2023  
上述产品符合《强制性产品认证实施规则 照明电器》(CNCA-C10-01:2014) 的要求, 特发此证。

发证日期: 2025 年 11 月 26 日 有效期至: 2030 年 02 月 18 日

本证书为变更证书, 证书首次颁发日期: 2025 年 02 月 19 日  
证书信息和有效性可扫描下方二维码或登录发证机构网站查验,  
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE



中国质量认证中心有限公司



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

**CERTIFICATE NO.:** 2025011002755791

**NAME AND ADDRESS OF THE APPLICANT**

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND ADDRESS OF THE MANUFACTURER**

Signify Netherlands B.V.  
High Tech Campus 48, 5656 AE Eindhoven, The Netherlands

**NAME AND LOCATION OF THE FACTORY**

**PRODUCT NAME,MODEL AND SPECIFICATION**

A.C. or D.C. Supplied Electronic Controlgears For LED Modules (LED Driver, Built-in, Auto-wound Controlgear, Constant Current Mode, ta: 60°C, tc: 90°C, EL, Temperature Declared Thermally Protected: 110°C, Controlled Port Dimming)  
See Appendix. 220-240V ~ 50/60Hz , 186-250Vdc

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023  
This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

**Valid from:** Nov.26,2025      **Valid until:** Feb.18,2030

Date of original issued: Feb.19,2025

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





# 中国国家强制性产品认证证书

证书编号：2025011002755791

证书附页：第 1 页 共 1 页

| 型号  | 输入                                     | 输出电流<br>(A) | 输出电压<br>(Vdc) | 最大工作<br>电压<br>(Vdc) | 输出功<br>率<br>(W) |
|---|--|-------------|---------------|---------------------|-----------------|
| Xitanium 75W<br>0.15-0.5A 220V<br>iXt TD 230V | 220-240V~<br>50/60Hz<br>0.35A<br>79.8W | 0.15-0.5    | 50-220        | 250                 | 75              |
|   | 186-250Vdc<br>0.32-0.43A<br>79.8W      |             |               |                     |                 |

本页为证书附页，应与证书主页同时使用。



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司