Ref. Certif. No.

NL-126239

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Electronic Controlgear for LED modules
Name and address of the applicant	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the manufacturer	Signify Netherlands B.V. High Tech Campus 48, 5656 AE Eindhoven, Netherlands
Name and address of the factory	
When more than one factory	☒ Additional information on page 3
Ratings and principal characteristics	**Product data** Ratings: Xi FP 22W 0.2-0.7A SNLDAE 230V C123 sXt Uin: 220-240 Vac, Iin: 0,12-0,11 Aac; fn: 50/60 Hz, DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,09-0,006 Adc; Pin: 26 W; Uoutput: 16-48 Vdc, Uout: 70 Vdc max; Prated: 22 W; Irated: 200-700 mA; tc: 85 °C; ta: -40… +55 °C; SELV; Built-in Xi FP 22W 0.3-1.0A SNLDAE 230V C123 sXt Uin: 220-240 Vac, Iin: 0,12-0,11 Aac; fn: 50/60 Hz, DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,09-0,006 Adc; Pin: 26 W; Uoutput: 8-32 Vdc, Uout: 50 Vdc max; Prated: 22 W; Irated: 300-1050 mA; tc: 85 °C; ta: -40… +55 °C; SELV; Built-in Xi FP 40W 0.2-0.7A SNLDAE 230V C123 sXt Uin: 220-240 Vac, Iin: 0,21-0,19 Aac; fn: 50/60 Hz, DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,15-0,01 Adc; Pin: 46 W; Uoutput: 25-77 Vdc, Uout: 100 Vdc max; Prated: 40 W; Irated: 200-700 mA; tc: 85 °C; ta: -40… +55 °C; SELV; Built-in Xi FP 40W .2-.7A SNLDAE 230 C123 TR sXt Uin: 220-240 Vac, Iin: 0,21-0,19 Aac; fn: 50/60 Hz; PF: 0,95; Pin: 46 W; Uoutput: 25-77 Vdc, Uout: 100 Vdc max; Prated: 40 W; Irated: 200-700 mA; tc: 85 °C; ta: -40… +55 °C; SELV; Built-in Xi FP 40W 0.3-1.0A SNLDAE 230V C123 sXt Uin: 220-240 Vac, Iin: 0,21-0,19 Aac; fn: 50/60 Hz, DC; PF: 0,95; Uin: 186-250 Vdc; Iin: 0,15-0,01 Adc; Pin: 46 W;

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-05-28

Signature: May Liu

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

	Uoutput: 20-54 Vdc, Uout: 60 Vdc max; Prated: 40 W; Irated: 300-1050 mA; tc: 85 °C; ta: -40… +55 °C; SELV; Built-in
Trademark / Brand (if any)	PHILIPS, SIGNIFY, ADVANCE or XITANIUM
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Xi FP 22W 0.2-0.7A SNLDAE 230V C123 sXt, Xi FP 22W 0.3-1.0A SNLDAE 230V C123 sXt, Xi FP 40W .2-.7A SNLDAE 230 C123 TR sXt, Xi FP 40W 0.2-0.7A SNLDAE 230V C123 sXt and Xi FP 40W 0.3-1.0A SNLDAE 230V C123 sXt
Additional information	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61347-1:2015, IEC 61347-1:2015/AMD1:2017, IEC 61347-2-13:2014, IEC 61347-2-13:2014/AMD1:2016 and IEC 62384:2020 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	6271096.50 and 6271096.51

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-05-28

Signature: May Liu

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

Additional factory

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands

Date: 2026-05-28

Signature: May Liu