



Semi-deep Recessed Family

RS280 G2 RC Rd D75 11W 30K 24D

Semi-deep Recessed Family, 11 W, 950 lm, 3000 K, Metallic grey

Bring superiority lighting effect together with low glare performance. Slim design with fit for majority of the installation requirement. 8mm trim can blend into the all kinds of the home deco style.

Product data


| General Information | | Power Consumption | |
|------------------------------------|----------------|--|--------------------------|
| Light source replaceable | No | Power Factor (Fraction) | 0.5 |
| Driver included | Yes | Connection | Flying leads/wires |
| Warranty period | 1 years | Number of products on MCB of 16 A type B | 88 |
| Light Technical | | Protection class IEC | Safety class II |
| Luminous Flux | 950 lm | Controls and Dimming | |
| Correlated Color Temperature (Nom) | 3000 K | Dimmable | No |
| Luminous Efficacy (rated) (Nom) | 86 lm/W | Constant light output | No |
| Color rendering index (CRI) | 90 | Mechanical and Housing | |
| Light source color | 930 warm white | Housing Material | Plastic |
| Luminaire light beam spread | 24° | Reflector material | - |
| Unified glare rating CEN | 13 | Housing Color | Metallic grey |
| Operating and Electrical | | Overall height | 77 mm |
| Input Voltage | 220 to 240 V | Overall diameter | 85 mm |
| Input Frequency | 50 or 60 Hz | Ingress protection code | IP20 [Finger-protected] |
| Inrush current | 12 A | Mech. impact protection code | IK03 [0.35 J reinforced] |

Semi-deep Recessed Family



| | |
|--|---|
| Net Weight (Piece) | 0.176 kg |
| Approval and Application | |
| Insulation Coverage Rating | Non IC Rating |
| Flammability mark | For mounting on normally flammable surfaces |
| EU RoHS compliant | Yes |
| Ambient temperature range | -20 to +40 °C |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.4359, 0.3963) 5SDCM |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Median useful life L70B50 | 25,000 hour(s) |

| | |
|---------------------------------|--------------------------------|
| Product Data | |
| Order product name | RS280 G2 RC Rd D75 11W 30K 24D |
| Full product name | RS280 G2 RC Rd D75 11W 30K 24D |
| Full product code | 694197061752900 |
| Order code | 929004120010 |
| Material Nr. (12NC) | 929004120010 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6941970617529 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 6941970617536 |

Dimensional drawing



Photometric data



Accent Lighting Spots - RS280 G2 RC Rd D75 11W 30K 24D

Light Distribution Diagram - RS280 G2 RC Rd D75 11W 30K 24D

Semi-deep Recessed Family

