



3

4

5

⊕

N

L

PHILIPS
LED 控制裝置 / LED драйвер
XITANIUM
Xi 19W 200-350mA 54V DS 230V EL G5

9290 048 311
Made in China/中國製造
Signify, IBRS 10461, 5600 VB, NL
Signify Commercial UK Limited
2 Guildford Business Park, GU2 8XG, UK

UK
CA

CE

EAC

CCC

05

Pin: 21W Prated: 19W
Uin: 220-240V~ Uoutput: 30-54Vdc
Iin: 0.1-0.035A~ Irated: 0.2/0.25/
Uin: 186-250V~ Iin: 0.3/0.35A
Iin: 0.12-0.03A~ Ie: -30...+55°C
Freq: 50/60HzDC Ie: 75°C
PF: 0.95 | output not mains isolated

EL

Excl. high risk task areas

8.5...9.5mm
0.5...1.5°

* t_c

OFF ↔ ON

1 2 NO

Rated selection

Prated	Irated	Pin1	Pin2
10.8W	0.2A	ON	ON
13.5W	0.25A	ON	OFF
16.2W	0.3A	OFF	ON
19W	0.35A	OFF	OFF

LED output
Uout=220Vdc max

Specification B:

Material: Fasson AW3209 or A7SG3
Adhesive: permanent
Background color: White
Printings color: Black 黑字
Fonts: Centrale Sans; 黑体
The label dimension: 108x23mm
Printing Quality: Water and petrol resistant
Packing: Reel inside Diameter 76mm
Reel outside Diameter <300mm
Keep blank 50cm each from the beginning and end
label Size : Length= A+/-0.1mm; Width=B+/-0.1mm
Distance between labels: C=3mm+/-0.1mm
Distance between label edge & backing paper : D=3+/-0.5mm

Change from Uout 200V to 220V

Change from PF 0.9C to 0.95

			Type Plate		4422 800 1524		1	07-18-25 A
			Xi 19W 200-350mA 54V DS 230V EL G5 (for XM)				1	08-13-25 B
							1	09-02-25 C
C	CR-XXXXXX	25.09.02						
REV	CHANGE NO	DATE						
DRAWN BY: Michael Lin			CHECKED BY STL	CHECKED BY ENGINEER:	SH 114 - 1	1 SH	10	A4
REVISED BY			CHECKED BY CE	APPROVED BY PM	SIGNIFY (CHINA) INVESTMENT CO., LTD.			