



3

4

5

±

N

L

PHILIPS
LED 控制裝置 / LED драйвер
XITANIUM
Xi 44W 200-350mA 125V DS 230V EL G5

9290 048 312
Made in China/中國製造
Signify, IBRS 10461, 5600 VB, NL
Signify Commercial UK Limited
2 Guildford Business Park, GU2 8XG, UK

44W LED

Pin: 48W

Uin: 220-240V~

Uin: 186-250V ~

Uout: 0.26-0.066A

Freq: 50/60HzDC

PF: 0.95

Rated: 44W

Uoutput: 60-125Vdc

Irated: 0.2/0.25/0.3/0.35A

ta: -30...+55°C

tc: 85°C

output not mains isolated

EL

Excl. high risk task areas

0.5...1.5°

0.5

Rated selection

Rated	Irated	Pin1	Pin2
25W	0.2A	ON	ON
34W	0.25A	ON	OFF
37.5W	0.3A	OFF	ON
44W	0.35A	OFF	OFF

OFF ↔ ON

1

2

NO

LED +

1

LED -

2

Specification B:

Material: Fasson AW3209 or A7SG3
Adhesive: permanent
Background color: White
Printings color: Black 黑字
Fonts: Centrale Sans; 黑体
The label dimension: 108x23mm
Printing Quality: Water and petrol resistant
Packing: Reel inside Diameter 76mm
Reel outside Diameter <300mm
Keep blank 50cm each from the beginning and end
label Size : Length= A+/-0.1mm; Width=B+/-0.1mm
Distance between labels: C=3mm+/-0.1mm
Distance between label edge & backing paper : D=3+/-0.5mm

Change from Uout 200V to 220V

Change from PF 0.9C to 0.95

			Type Plate		4422 800 1525		1 07-18-25 A	
			Xi 44W 200-350mA 125V DS 230V EL G5 (for XM)				1 08-13-25 B	
C	CR-XXXXXX	25.09.02					1 09-02-25 C	
REV	CHANGE NO	DATE						
DRAWN BY: Michael Lin			CHECKED BY STL	CHECKED BY ENGINEER:	SH 114 - 1	1 SH	10	A4
REVISED BY			CHECKED BY CE	APPROVED BY PM	SIGNIFY (CHINA) INVESTMENT CO., LTD.			