



3

⊕

4

N

5

L

PHILIPS
LED 控制裝置 / LED драйвер
XITANIUM
Xi 65W 200-350mA 185V DS 230V EL G5

65W LED
9290 048 313
Made in China / 中國製造
Signify, IBRS 10461, 5600 VB, NL
Signify Commercial UK Limited
2 Guildford Business Park, GU2 8XG, UK

UK CA

CE

EAC

CCC

05

Pin: 69W / Uin: 220-240V~ / Uin: 0.33-0.12A~ / Uin: 186-250V ~- / Iin: 0.39-0.11A ~- / Freq: 50/60Hz±DC / PF: 0.95

Rated: 65W / Uoutput: 120-185Vdc / Irated: 0.2/0.25 / 0.3/0.35A / Tc: -30...+55°C / Tc: 85°C / output not mains isolated

EL

Excl. high risk task areas

8.5...9.5mm

0.5...1.5°

* Tc

Rated selection

Rated	Irated	Pin1	Pin2
37W	0.2A	ON	ON
45W	0.25A	ON	OFF
55W	0.3A	OFF	ON
65W	0.35A	OFF	OFF

OFF ↔ ON

1

2


NO

LED +

1

LED -

2



Specification B:

Material: Fasson AW3209 or A7SG3

Adhesive: permanent

Background color: White

Printings color: Black 黑字

Fonts: Centrale Sans; 黑体

The label dimension: 108x23mm

Printing Quality: Water and petrol resistant

Packing: Reel inside Diameter 76mm


Reel outside Diameter <300mm

Keep blank 50cm each from the beginning and end

label Size : Length= A+/-0.1mm; Width=B+/-0.1mm

Distance between labels: C=3mm+/-0.1mm

Distance between label edge & backing paper : D=3+/-0.1mm



Change from Pin 68W to 69W

			Type Plate			4422 800 1526			1	08-07-25 A
			Xi 65W 200-350mA 185V DS 230V EL G5						1	09-02-25 B
			(for XM)							
B	CR-XXXXXX	25.09.02								
REV	CHANGE NO	DATE								
DRAWN BY: Michael Lin			CHECKED BY STL		CHECKED BY ENGINEER:		SH 114 - 1	1 SH	10	A4
REVISED BY			CHECKED BY CE		APPROVED BY PM		SIGNIFY (CHINA) INVESTMENT CO., LTD.			