



中国国家强制性产品认证证书

证书编号：2026011002851800

认证委托人名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交直流电子控制装置（LED 控制装置，独立式，恒流模式，安全特低电压，EL，控制端口调光：DALI 调光， t_a : 50°C/60°C， t_c : 90°C，定温热保护：110°C，II 类，IP20，适宜直接安装在普通可燃材料表面）
见附页；220-240V~50/60Hz，186-250VDC

产品标准和技术要求

GB 17625.1-2022; GB/T 17743-2021; GB/T 19510.1-2023; GB/T 19510.213-2023

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2026 年 03 月 13 日 有效期至：2031 年 03 月 12 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2026011002851800

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. or D.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Independent, Constant Current Mode, SELV, EL, Controlled Port Dimming: DALI Dimming, ta:50°C/60°C, tc:90°C, Temperature Declared Thermally Protected: 110°C, Class II, IP20, Suitable For Direct Mounting On Normally Flammable Material Surfaces)
See Appendix ; 220-240V~ 50/60Hz , 186-250VDC

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023
This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Mar.13,2026

Valid until: Mar.12,2031

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





中国国家强制性产品认证证书

证书编号：2026011002851800

证书附页：第 1 页 共 1 页

XITANIUM 50W WH 0.7-1.5A 54V TD DS 230V 输出：50Wmax 0.7-1.5A 24-54Vdc Uout=60V
ta: 50°C,

XITANIUM 36W WH 0.15-1.05A 54V TD DS 230V 输出：36Wmax 0.15-1.05A 24-54Vdc
Uout=60V ta: 60°C;

输入：220-240V 50/60Hz 186-250VDC

本页为证书附页，应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司