



ECO HOME

18 W (75 W) Compact fluorescent Luster bulb

Eco Home is the basic energy saver among Philips compact fluorescent lamps, offering great value for money with quality and performance you can trust. It is an ideal high-quality energy-saving replacement for incandescent light bulbs, consuming up to 80% less energy than standard incandescent bulbs and lasting for up to 6 years (based on average residential usage of 1,000 hours a year or 3 hours a day).

Product data

General Information	
Cap-Base	E27
Nominal lifetime	8,000 hour(s)
Switching Cycle	5,000
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,067 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	58 lm/W
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	50 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz


Power Consumption	18.0 W
Lamp Current (Nom)	245 mA
Starting Time (Nom)	0.3 s
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Stick
Net Weight (Piece)	0.065 kg
Approval and Application	
Mercury (Hg) Content (Max)	2 mg
Energy Consumption kWh/1000 h	18 kWh
Product Data	
Order product name	18 W (75 W) Compact fluorescent Luster bulb
Full product name	18 W (75 W) Compact fluorescent Luster bulb
Full product code	871829165077500

ECO HOME

Order code	929689013802
Material Nr. (12NC)	929689013802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291650775

Numerator - Packs per outer box	6
EAN/UPC - Case	8718291650782

Dimensional drawing



Product	D (max)	C (max)	F (max)
18 W (75 W) Compact fluorescent Luster bulb	36.0 mm	143 mm	48.4 mm

