


Outdoor

Poles and Brackets

P9300 Straight Round Fluted



example: P9300 10 A T D

4" Straight Flat Fluted w/3" tenon

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Order guide

Product Code P9300	Pole Height	Finish	Outlet Location	Outlet Options	
P9300	10' 12' 14' 16'	A Black B White G Verde H Bronze	T 12" Down from Top - Aligned with House Side	D Standard Duplex G GFI Duplex	
	16	J Green			

Note: Wall thickness is 0.125 aluminum. EPA values based on destructive break testing. For AASHTO ratings, contact factory.

Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)	Hand Hole Dim (in)
P9300	Round	Straight	4	Fluted	round	7	9 x 0	2 x 4

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	Anchor Bolts (in)
P9300	P9300-10	10	3	0.188 - 0.313	16.65	10.15	3/4-19 bs
P9300	P9300-12	12	3	0.188 - 0.313	13.59	8.08	3/4-19 bs
P9300	P9300-14	14	3	0.188 - 0.313	8.97	5.16	3/4-19 bs
P9300	P9300-16	16	3	0.188 - 0.313	7.38	4.03	3/4-19 bs

 ${\sf EPA}\ {\sf values}\ {\sf based}\ {\sf on}\ {\sf destructive}\ {\sf break}\ {\sf testing}.\ {\sf For}\ {\sf AASHTO}\ {\sf ratings}, {\sf contact}\ {\sf factory}.$

Specifications

HOUSING:

356-T6 Sand Cast Aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel. Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:


Please visit **www.signify.com/warranties** for more details on structural and finish warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dualfunction indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistan

P9300 Poles and Brackets

Straight Round Fluted



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 signify Canada Ltd. 181 Hillmount Road, Markham, ON, Canada L6C 2S3 Salanhona 800-668-9008