



The **C4XC Series** is a NEMA 4X Exit combo. Featuring a reinforced polycarbonate housing, the C4XC series can be wall, ceiling or end mounted.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide

Example: C4XC-R-CT-W-115-6

Family	Letter Color	Self Diagnostics	Housing	Faces/Wattage	Voltage
C4XC NEMA 4X Combo	R Red G Green	Blank CT Self diagnostic	W White B Black	115 Single Face, 15W 212 Double Face, 12W	6 6 Volts

Specifications

Codes and standards

- UL listed to standard 924
- NEMA 4X, IP66 and NSF rated
- NFPA 101 (Life Safety Code)
- UL listed for wet locations (0° C - 50° C)

Power consumption

- All models dual voltage 120/277

Construction

- Housing constructed of reinforced polycarbonate
- High impact resistant, UV stabilized polycarbonate clear lens

Lamps

- High brightness white LEDs
- 3.6W LED lamp heads x 2
- Adjustable lamp heads provide optimal center to center spacing

Mounting

- Universal knockout pattern on back provided with gasket for watertight seal for wall mounting
- Polycarbonate mounting canopy included for ceiling or end mounting

Battery

- Maintenance-free, 6V/12V rechargeable NiCd (NiCad) battery (12W, 15W models)

Options

- Self-diagnostic feature performs monthly, biannual, and annual tests to ensure reliable operation and meet electrical and life safety codes

Electronics

- Charge rate/power "ON" LED indicator light and magnetic test switch for mandated code compliance testing
- Internal solid-state transfer switch automatically connects the internal battery to the LED board for minimum 90-minutes emergency illumination

Warranty

- Five year limited warranty on all electronics and housing, battery prorated for 5 years

