



The **C4XC Series** is a NEMA 4X Exit combo. Featuring a reinforced polycarbonate housing, the C4XC series can be wall, ceiling or end mounted.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

Example: C4XC-R-CT-W-1-12-6

Family	Letter Color	Self Diagnostics	Housing	Faces	Wattage	Voltage
C4XC NEMA 4X Combo	R Red G Green	Blank CT Self diagnostic	W White B Black	1 Single 2 Double	12 12 Watts 15 15 Watts	6 6 Volts

Specifications

Codes and standards

- UL listed to standard 924
- NEMA 4X, IP66 and NSF rated
- NFPA 101 (Life Safety Code)
- UL listed for wet locations (0° C - 50° C)

Power consumption

- All models dual voltage 120/277

Construction

- Housing constructed of reinforced polycarbonate
- High impact resistant, UV stabilized polycarbonate clear lens

Mounting

- Universal knockout pattern on back provided with gasket for watertight seal for wall mounting
- Polycarbonate mounting canopy included for ceiling or end mounting

Battery

- Maintenance-free, 6V/12V rechargeable NiCd (NiCad) battery (12W, 15W models)

Options

- Self-diagnostic feature performs monthly, biannual, and annual tests to ensure reliable operation and meet electrical and life safety codes

Electronics

- Charge rate/power "ON" LED indicator light and magnetic test switch for mandated code compliance testing
- Internal solid-state transfer switch automatically connects the internal battery to the LED board for minimum 90-minutes emergency illumination
- Available 4.8W, 7.8W, 20.8W remote capability (6V/12V DC output) standard on the 12W and 15W models

Warranty

- Five year limited warranty on all electronics and housing, battery prorated for 5 years

