



The **C4XU Series** is a NEMA 4X exit unit. Featuring a reinforced polycarbonate housing, the C4XU series can be wall mounted in a variety of applications and environments.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

#### Ordering guide

Example: C4XU-CT-W-15

Family	Self Diagnostics	Housing	Wattage
C4XU NEMA 4X Emergency	Blank	W White	15 15 Watts
	CT Self diagnostic	B Black	36 36 Watts

#### Specifications

##### Codes and standards

- UL listed to standard 924
- NFPA 101 (Life Safety Code)
- NEMA 4X, IP66 and NSF rated
- UL listed for wet locations (0° C - 50° C), 15W and (10 C- 40 C), 36W

##### Lamps

- Two fully adjustable, 3.3 watt high performance round MR16 lamp heads provide optimal light distribution for optimized center to center spacing

##### Power consumption

- All models dual voltage 120/277

##### Construction

- Housing constructed of reinforced polycarbonate enclosure with high-impact UV stabilized polycarbonate clear lens
- Fully gasketed with stainless steel screws

##### Mounting

- Universal knockout pattern on back provided with gasket for watertight seal for wall mounting

##### Battery

- Maintenance-free, 6V/12V rechargeable NiCd (NiCad) battery (15W models), 6V/12V maintenance free rechargeable sealed lead acid battery (36W models)

##### Electronics

- Charge rate/power "ON" LED indicator light and magnetic test switch for mandated code compliance testing
- Internal solid-state transfer switch automatically connects the internal battery to lamp heads for minimum 90-minute emergency illumination

##### Options

- Self-diagnostic feature performs monthly, biannual, and annual tests to ensure reliable operation and meet electrical and life safety codes

##### Warranty

- Five year limited warranty on all electronics and housing. Battery prorated for 5 years (Ni-Cd), 2 years (sealed lead-acid)

