



Item	Value	Unite
A1	280.0 (+0.2/-0.2)	mm
A2	270.0 (+0.2/-0.2)	mm
B1	30.0 (0.2/-0.2)	mm
C1	21.0 (+0.2/-0.2)	mm
D1	4.1 (+0.1/-0.1)	mm

Signify (China) Investment Co., Ltd.
All rights are reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.

GB/T 1804-2000m (Unit: mm)									
SIZE RANGE	0.5-3	>3-6	>6-30	>30-120	>120-400	>400-1000			
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	ITEM	ASSEMBLY NO.	QUANT.
GENERAL ROUGHNESS	UNIT: mm	MATERIAL						MODEL NAME	
SCALE	PROJECT TYPE	TREATMENT						ORDER NO.	QUANT.

TITLE: Xitanium 150W 0.2-0.7A 300V iXt TD 230V
Xitanium 100W 0.15-0.5A 300V iXt TD 230V

PART NUMBER: 929003976606
929003976506

2024-09-03 A

REV | CHANGE NO. | DATE

DESIGNED BY G.Sun	CHECKED BY	1 SH.	SH. 112 of 1	FORM NO.	A3
DRAWN BY Yapeng.LIN	APPROVED BY	REVISED BY			

TLD
HID