

1 2 3 4 5 6 7 8 9 10

Signify

A

B

C

D

E

F

G

H

B1

C1

D1

A2

A1

Item	Value	Unite
A1	280.0 (+0.2/-0.2)	mm
A2	270.0 (+0.2/-0.2)	mm
B1	30.0 (0.2/-0.2)	mm
C1	21.0 (+0.2/-0.2)	mm
D1	4.1 (+0.1/-0.1)	mm



GB/T 1804-2000m (Unit: mm)											
SIZE RANGE	0.5-3	>3-6	>6-30	>30-120	>120-400	>400-1000		ITEM	ASSEMBLY NO.	QUANT.	
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8					
GENERAL ROUGHNESS	UNIT	MATERIAL						MODEL NAME			
✓	mm										
SCALE	PROJECT TYPE	TREATMENT						ORDER NO.		QUANT.	
		TITLE: Titanium 150W 0.2-0.7A 300V iXt TD 230V Titanium 100W 0.15-0.5A 300V iXt TD 230V						PART NUMBER: 929003976606 929003976506		2024-09-03 A	
REV. CHANGE NO. DATE											
DESIGNED BY		G.Sun		CHECKED BY		1 SH.		SH. 112 of 1		FORM NO. A3	
DRAWN BY		Yapeng.LIN		APPROVED BY		REVISED BY		SIGNIFY (CHINA) INVESTMENT CO., LTD.			

1 2 3 4 5 6 7 8 9 10

Signify (China) Investment Co., Ltd.
All rights are reserved. Reproduction in whole or in part is
prohibited without the written consent of the copyright owner.

TLD	
HID	