



中国国家强制性产品认证证书

证书编号：2024011002732745

认证委托人名称及地址
昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址
昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格
LED 模块用交流电子控制装置（LED 控制装置，内装式，恒流模式，自耦式，不可调光，定温热保护：110℃）
见附页。220-240V~ 50/60Hz

产品标准和技术要求
GB 17625.1-2022; GB/T 17743-2021; GB/T 19510.1-2023; GB/T 19510.213-2023
上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2024 年 12 月 03 日 有效期至：2029 年 12 月 02 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024011002732745

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China.

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai City, P.R.China.

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME,MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (Built-in, Constant Current Mode,
Auto-wound Controlgear, Non-dimmable, Temperature Declared Thermally Protected:110℃)
See Appendix. 220-240V ~ 50/60Hz

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022;GB/T 17743-2021;GB/T 19510.1-2023;GB/T 19510.213-2023

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014).

Valid from: Dec.03,2024

Valid until: Dec.02,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





中国国家强制性产品认证证书

证书编号: 2024011002732745

证书附页: 第 1 页 共 1 页

序号	产品型号	参数																		
1.	Xitanium 65W 200-350mA 185V DS 230V CCT	输出 1 (WW) /2 (CW) /1 (WW) +2 (CW): 0.20/0.25/0.3/0.35A (恒流, 拨码开关调节), 120-185V $\overline{\text{=}}$, Uout=250V $\overline{\text{=}}$, 配套 Max.65W LED 模块; tc: 85°C																		
2.	Xitanium 44W 200-350mA 125V DS 230V CCT	输出 1 (WW) /2 (CW) /1 (WW) +2 (CW): 0.20/0.25/0.3/0.35A (恒流, 拨码开关调节), 70-125V $\overline{\text{=}}$, Uout=220V $\overline{\text{=}}$, 配套 Max.44W LED 模块; tc: 85°C																		
3.	Xitanium 19W 200-350mA 54V DS 230V CCT	输出 1 (WW) /2 (CW) /1 (WW) +2 (CW): 0.20/0.25/0.3/0.35A (恒流, 拨码开关调节), 30-54V $\overline{\text{=}}$, Uout=220V $\overline{\text{=}}$, 配套 Max.19W LED 模 块; tc: 75°C																		
输入: 220-240V $\sim$, 50/60Hz;  , 自耦式, 内装式, 恒流模式																				
备注: 1.CCT 开关 CW 档时输出 2 (CW) 单路输出, NW 档时输出 1 (WW) 和 输出 2 (CW) 双路输出, WW 档时输出 1 (WW) 单路输出。 2.拨码开关																				
<table><tr><th colspan="3">Rated selection</th></tr><tr><th>Irated</th><th>Pin1</th><th>Pin2</th></tr><tr><td>0.20A</td><td>ON</td><td>ON</td></tr><tr><td>0.25A</td><td>ON</td><td>OFF</td></tr><tr><td>0.30A</td><td>OFF</td><td>ON</td></tr><tr><td>0.35A</td><td>OFF</td><td>OFF</td></tr></table>			Rated selection			Irated	Pin1	Pin2	0.20A	ON	ON	0.25A	ON	OFF	0.30A	OFF	ON	0.35A	OFF	OFF
Rated selection																				
Irated	Pin1	Pin2																		
0.20A	ON	ON																		
0.25A	ON	OFF																		
0.30A	OFF	ON																		
0.35A	OFF	OFF																		

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司