



产品认证证书

证书编号: CQC21010309621

发证日期: 2021年08月18日

有效期至: 长期有效

委托人名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

制造商名称 昕诺飞(中国)投资有限公司
及注册地址 上海市闵行区田林路888弄9号楼

生产企业名称
及生产地址

产品名称和系列、规格、型号 普通照明用LED模块(内装式, $t_c: 85^{\circ}\text{C}$, RG1)
见附件; 输入: 24Vdc

产品标准和技术要求 GB 19510.1-2009; GB 24819-2009; IEC/TR62778-2014

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-465393-2016 认证规则的要求, 特发此证。
本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



签发:

谢肇熙



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C 0507859



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC21010309621

Valid from: Aug.18,2021

Valid until:long-term

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

**PRODUCT NAME, MODEL
AND SPECIFICATION**

LED Modules For General Lighting Services (Built-In, tc:85°C, RG1)
See Appendix ; Input : 24Vdc

**THE STANDARDS AND
TECHNICAL REQUIREMENTS
FOR THE PRODUCTS**

GB 19510.1-2009;GB 24819-2009;IEC/TR62778-2014

**TYPE OF CERTIFICATION
SCHEMES**

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-465393-2016.
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C 0507859



产品认证证书

证书编号: CQC21010309621

第 1 页 共 2 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 507859

序号	型号	最大使用长度 (m)	输入电压	电流 (A/m)	功率 (W/m)	LED 颗粒数 (颗/m)	单颗 LED 功率(W)	相关色温 (K)
1	Fortimo LEDFlex C 5m 500lm/m 927 C5 G1	5	24VDC	0.254	6.1	352	0.0173	2700
2	Fortimo LEDFlex C 5m 500lm/m 930 C5 G1	5	24VDC	0.242	5.8	352	0.0165	3000
3	Fortimo LEDFlex C 5m 500lm/m 935 C5 G1	5	24VDC	0.238	5.7	352	0.0162	3500
4	Fortimo LEDFlex C 5m 500lm/m 940 C5 G1	5	24VDC	0.221	5.3	352	0.0151	4000
5	Fortimo LEDFlex C 5m 500lm/m 965 C5 G1	5	24VDC	0.217	5.2	352	0.0148	6500
6	Fortimo LEDFlex C 5m 1000lm/m 927 C5 G1	5	24VDC	0.517	12.4	352	0.0352	2700
7	Fortimo LEDFlex C 5m 1000lm/m 930 C5 G1	5	24VDC	0.500	12	352	0.0341	3000
8	Fortimo LEDFlex C 5m 1000lm/m 930	5	24VDC	0.500	12	352	0.0341	3000 PW



中国质量认证中心



产品认证证书

证书编号: CQC21010309621

第 2 页 共 2 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 507859

	PW C5 G1							
9	Fortimo LEDFlex C 5m 1000lm/m 935 C5 G1	5	24VDC	0.483	11.6	352	0.0330	3500
10	Fortimo LEDFlex C 5m 1000lm/m 940 C5 G1	5	24VDC	0.450	10.8	352	0.0307	4000
11	Fortimo LEDFlex C 5m 1000lm/m 965 C5 G1	5	24VDC	0.442	10.6	352	0.0301	6500

附件



中国质量认证中心