


# GP Teardrop Cleanroom G2/ 泪滴型LED洁净室灯具

## CR388C


Mounting instruction/ 安装说明

CR388C-M002

|  | <b>GB</b><br>7000   | <b>IEC</b><br>EN60598      | <b>GB</b><br>24461                                                                | <b>ta</b><br>25 °C | <b>IP40</b> |  |  |  |
|-----------------------------------------------------------------------------------|---------------------|----------------------------|-----------------------------------------------------------------------------------|--------------------|-------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|
| Type Desc<br>型号描述                                                                 | Pmax.(W)<br>灯具功率(W) | Voltage/Frequency<br>电压/频率 |  | CCT<br>色温          |             |                                                                                   |                                                                                   |                                                                                    |
| CR388C LED20 LI20 PSU                                                             | 16                  | 220-240V 50/60Hz           | 0.9                                                                               | CW (冷白光) /NW (正白光) |             |                                                                                   |                                                                                   |                                                                                    |
| CR388C LED20 Amber LI20 PSU                                                       | 21                  | 220-240V 50/60Hz           | 1.2                                                                               | Amber (黄光)         |             |                                                                                   |                                                                                   |                                                                                    |




### 1



保存好  
Keep it

### 2



飞利浦不提供螺钉&垫片  
Screws&washers is not provided by Philips

### 3

#### Connect entry cable 连接电源线


Recommend to use junction box, IP grade  $\geq$  IP40, dimension  $\geq$  10x20x25 mm, it is not provided by Philips.  
请使用 IP40 以上的接线盒（接线端子尺寸不小于 10x20x25mm），飞利浦不提供接线盒。

**PSU Luminaire cable/PSU 灯具出线：**  
60227 IEC57 3x1mm<sup>2</sup>  
L: Brown/棕; N: Blue/蓝; G: Yellow+Green/黄绿;

**PSD Luminaire cable/PSD 灯具出线：**  
60227 IEC57 5x1mm<sup>2</sup>  
L: Brown/棕; N: Blue/蓝; G: Yellow+Green/黄绿;

DALI Tx(D+): Gray/灰; DALI Tx(D-): White/白

### 4



咔哒 Click





- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements  
灯具应由有资格的电工安装，接线要符合 IEE 电气标准或国家标准。
- Do not switch on before complete installation.  
接线过程中，切勿通电。
- Luminaire application, customer should consult clean room experts.  
灯具选用，请咨询洁净室应用专家。
- The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc must be avoided during the use and storage.  
灯具避免在腐蚀性环境或者含有有害物质，例如硫化物，卤化物，邻苯二甲酸酯等环境中存储和使用。
- The luminaire with type Y attachment. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or similar qualified person in order to avoid a hazard.  
Y型连接灯具。如果此灯具的外部软缆或软线损坏了，该线要由制造商或其服务代理商或有类似资格的人更换，以避免发生危险。
- The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.  
此灯具内的光源应由制造商或其服务代理商或一个有类似资格的人来更换。