


GP Teardrop Cleanroom G2/ 泪滴型LED洁净室灯具



CR388C

Mounting instruction/ 安装说明

CR388C-M002

	GB 7000	IEC EN60598	GB 24461	ta 25 °C	IP40			
Type Desc 型号描述	Pmax.(W) 灯具功率(W)	Voltage/Frequency 电压/频率		CCT 色温				
CR388C LED20 LI20 PSU	16	220-240V 50/60Hz	0.9	CW (冷白光) /NW (正白光)				
CR388C LED20 Amber LI20 PSU	21	220-240V 50/60Hz	1.2	Amber (黄光)				





- 
- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements
灯具应由有资格的电工安装，接线要符合 IEE 电气标准或国家标准。
 - Do not switch on before complete installation.
接线过程中，切勿通电。
 - Luminaire application, customer should consult clean room experts.
灯具选用，请咨询洁净室应用专家。
 - The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc must be avoided during the use and storage.
灯具避免在腐蚀性环境或者含有有害物质，例如硫化物，卤化物，邻苯二甲酸酯等环境中存储和使用。
 - The luminaire with type Y attachment. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or similar qualified person in order to avoid a hazard.
Y型连接灯具。如果此灯具的外部软缆或软线损坏了，该线要由制造商或其服务代理商或有类似资格的人更换，以避免发生危险。
 - The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
此灯具内的光源应由制造商或其服务代理商或一个有类似资格的人来更换。
- 