



中国国家强制性产品认证证书

证书编号：2024011002616389

认证委托人名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产者名称及地址

昕诺飞（中国）投资有限公司
上海市闵行区田林路 888 弄 9 号楼

生产企业名称及地址

产品名称和系列、型号、规格

LED 模块用交流电子控制装置（LED 控制装置，独立式，恒流模式，安全特低电压， $t_a: 50^{\circ}\text{C}$ ， $t_c: 75^{\circ}\text{C}$ ，II 类，IP20，适宜直接安装在普通可燃材料表面，定温热保护： 130°C ，不可调光）
见附页，220-240V~ 50/60Hz.

产品标准和技术要求

GB 17625.1-2022; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009

上述产品符合《强制性产品认证实施规则 照明电器》（CNCA-C10-01:2014）的要求，特发此证。

发证日期：2024 年 03 月 27 日 有效期至：2029 年 03 月 26 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

经中国合格评定国家认可委员会认可 CNAS C001-P



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024011002616389

NAME AND ADDRESS OF THE APPLICANT

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND ADDRESS OF THE MANUFACTURER

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

NAME AND LOCATION OF THE FACTORY

PRODUCT NAME, MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgear For LED Modules (LED Driver, Independent, Constant Current Mode, SELV, ta: 50°C, tc: 75°C, Class II, IP20, Suitable For Direct Mounting On Normally Flammable Material, Temperature Declared Thermally Protected: 130°C, Non-dimmable)
See Appendix; 220-240V ~ 50/60Hz.

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 17625.1-2022; GB/T 17743-2021; GB 19510.1-2009; GB 19510.14-2009
This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification (REFNO. CNCA-C10-01:2014).

Valid from: Mar.27,2024

Valid until: Mar.26,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



<http://www.cqc.com.cn>

Building 5, Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666



扫描全能王 创建



中国国家强制性产品认证证书

证书编号：2024011002616389

证书附页：第 1 页 共 1 页

序号	型号	输入 电流	输出 电流	最大输出电压	输出电压	输出 功率
1	CertaDrive 8W 0.2A 40V I 230V	0.05A	0.20A	Max. 60VDC	30-40VDC	8W
2	CertaDrive 10W 0.25A 40V I 230V	0.06A	0.25A	Max. 60VDC	30-40VDC	10W
3	CertaDrive 12W 0.3A 40V I 230V	0.07A	0.30A	Max. 60VDC	30-40VDC	12W
4	CertaDrive 14W 0.35A 40V I 230V	0.08A	0.35A	Max. 60VDC	30-40VDC	14W
5	CertaDrive 16W 0.4A 40V I 230V	0.10A	0.40A	Max. 60VDC	30-40VDC	16W
6	CertaDrive 18W 0.45A 40V I 230V	0.11A	0.45A	Max. 60VDC	30-40VDC	18W
7	CertaDrive 20W 0.5A 40V I 230V	0.12A	0.50A	Max. 60VDC	30-40VDC	20W

输入均为：220-240V~ 50/60Hz

本页为证书附页，应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

<http://www.cqc.com.cn>

北京市丰台区南四环西路188号九区5号楼 100070

电话：+86 10 83886666



扫描全能王 创建