

PHILIPS

CertaFlux

LED

CertaFlux RDL accessories



Datasheet

CertaFlux RDL LED system

Compact linear LED lighting for attractive merchandising

CertaFlux RDL portfolio is optimized for standard applications lengths with options for main cooler applications. A carefully-selected range of accessories is also available including mounting clips and cables.

December 2020



indirect




instant

Ordering data

Commercial product name	EOC	12NC	Box quantity
CertaFlux RDL clip canopy 0° surface	8718699 621148 00	9290 016 68606	100
CertaFlux RDL clip canopy 30° surface	8718699 621162 00	9290 016 68706	100
CertaFlux RDL clip shelf front	8718699 621063 00	9290 016 68806	100
CertaFlux RDL clip shelf arm	8718699 621025 00	9290 016 68906	100
CertaFlux RDL clip shelf magnetic	8718699 621100 00	9290 016 69006	100
InteGrade power cable 0.7m white	8718696 824474 00	9290 016 25306	96
InteGrade power cable 1m(39") black	8718291 218128 00	9290 006 41014	24
InteGrade power cable 2.5m(98") black	8718291 221449 00	9290 006 41114	24
InteGrade cable 1m(39") black angle	8718291 221364 00	9290 006 44614	24
InteGrade cable 2.5m(98") black angle	8718291 221463 00	9290 006 44814	24
InteGrade power cable 1m(39") white	8718291 221401 00	9290 006 45614	24
InteGrade power cable 1.85m white	8718696 824450 00	9290 016 25206	96
InteGrade power cable 2.5m(98") white	8718291 221487 00	9290 006 44514	24
InteGrade cable 1m(39") white angle	8718291 221425 00	9290 006 44714	24
InteGrade cable 2.5m(98") white angle	8718291 221500 00	9290 006 44914	24
InteGrade power cable 3m black angle	8718696 83041 300	9290 016 50106	24
InteGrade power cable 6m white	8718696 824375 00	9290 016 24806	12
InteGrade spacer cable 113mm white	8718696 824436 00	9290 016 25106	24
InteGrade spacer cable 0.3m black	8718696 824412 00	9290 016 25006	24
InteGrade spacer cable 0.5m black	8718291 221524 00	9290 006 45014	24
InteGrade spacer cable 0.5m white	8718291 221548 00	9290 006 45114	24
InteGrade spacer cable M 0.7m 5.5c black	8718696 824351 00	9290 016 24706	24
InteGrade extension cable 1.5m(59") black	8718291 707257 00	9290 008 74413	24
InteGrade Y cable black	8718291 707233 00	9290 008 74313	24

Mechanical characteristics



Absolute ratings

Parameter	Min	Max	Unit
Ambient temperature	-30	30	°C
Storage temperature	-30	60	°C



© 2020 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: 3 Guildford Business Park, GU2 8XG

08/12/2020