



## CoreLine Panel RC132V BN



			<b>RG0</b>	<b>220V 240V</b>	<b>50Hz 60Hz</b>		<b>Lifetime up to 100Khrs @L80</b>	<b>Ta 25 °C</b>	<b>Max. 35°C Min. -10°C</b>	<b>GLOW WIRE 650 C</b>	
--	--	--	------------	----------------------	----------------------	--	------------------------------------	-----------------	---------------------------------	------------------------	--

	IP	IK	L×W×H1(mm)	
RC132V G6 36S/840 PSU W60L60 OC BN	IP40/IP20	IK02	595x595x35	2.10
RC132V G6 36S/840 PSU W60L60 OC BN6	IP40/IP20	IK02	595x595x35	2.10
RC132V G6 43S/840 PSU W60L60 OC BN	IP40/IP20	IK02	595x595x35	2.10
RC132V G6 43S/840 PSU W60L60 NOC BN	IP40/IP20	IK02	595x595x35	1.60
RC132V G6 50S/840 PSU W60L60 OC BN	IP40/IP20	IK02	595x595x35	2.10
RC132V G6 50S/840 PSU W60L60 OC BN CL	IP40/IP20	IK02	595x595x35	2.10
RC132V G6 50S/840 PSD W60L60 OC BN	IP44/IP20	IK02	595x595x35	2.10

Energy efficiency class of light source  
**C**






VPC visible profile ceiling	SP suspended	SM surface mounted	PCV plaster ceiling

Available as accessory (Need to purchase separately)

	<b>Suspension set:</b> 911401809387 RC159Z Suspension set SME-4 WH (PSD) 911401809487 RC159Z Suspension set SME-3 WH (PSU)		<b>Safety cable:</b> 911401809187 RC159Z Safety Cable
	<b>Plaster ceiling set:</b> 911401809287 RC159Z Plaster Ceiling SMB-PLC		<b>Surface mounted set:</b> 911401807787 RC159Z SMB W60L60



### Power Connection





# VPC Visible Profile Ceiling/ Lay-In mounting




Optional with  
911401809187 RC159Z Safety Cable



1




## Safety cable



2

## Inrush current



	PSU			PSD
	26W	31W	38W	38W
<b>Electrical characteristics</b>				
<b>I<sub>max</sub> (A)</b>	16	20	22	19.6
<b>T<sub>ref</sub> (us)</b>	200	220	250	260
<b>MCB No. of luminaires max.</b>				
<b>B-10 A</b>	18	13	12	13
<b>B-16A</b>	30	21	20	22
<b>C-10 A</b>	32	23	21	23
<b>C-16A</b>	51	37	33	39