



EU Declaration of Conformity

Document No.: 2025A0124

Year in which CE Mark was first affixed: 2025

1. Product Range / Model:

Product Range / Model:

NAME: InteGrade engine G5

DESCRIPTION: LED module for Retail Display Lighting

BRAND: Philips

2. Manufacturer Name & Address:

Signify

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

3. This declaration of conformity is issued under the sole responsibility of the manufacturer.

4. Object of the declaration:

Product Code:

See tables on page 2 to 5

5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Low Voltage Directive (LVD), 2014/35/EU

- EN IEC 62031:2020 + A11:2021
- EN 62493 :2015+A1:2022

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN IEC 55015:2019 + A11:2020
- EN IEC 61547:2023

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- Commission Regulation (EU) 2019/2020 and amendment Commission Regulation (EU) 2021/341

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU and applicable Delegated Directives

- EN IEC 63000:2018

7. Additional information: The product in this declaration is produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Signed for and on behalf of:

Signify

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands



Hans Bellemans

Head of Quality OEM

2025-12-18, Eindhoven



EU Declaration of Conformity

Document No.: 2025A0124

Specification of the products:

12NC	Product Description	Brand	Remarks
929003977206	InteGrade engine Va 140mm WWR G5	Philips / Signify	
929003977306	InteGrade engine Va 575mm WWR G5	Philips / Signify	
929003977406	InteGrade engine Va 855mm WWR G5	Philips / Signify	
929003977506	InteGrade engine Va 1150mm WWR G5	Philips / Signify	
929003977606	InteGrade engine Va 140mm 956 G5	Philips / Signify	
929003977706	InteGrade engine Va 575mm 956 G5	Philips / Signify	
929003977806	InteGrade engine Va 855mm 956 G5	Philips / Signify	
929003977906	InteGrade engine Va 1150mm 956 G5	Philips / Signify	
929003978006	InteGrade engine Vi 140mm WWR G5	Philips / Signify	
929003978106	InteGrade engine Vi 575mm WWR G5	Philips / Signify	
929003978206	InteGrade engine Vi 855mm WWR G5	Philips / Signify	
929003978306	InteGrade engine Vi 1150mm WWR G5	Philips / Signify	
929003978406	InteGrade engine Vi 140mm 956 G5	Philips / Signify	
929003978506	InteGrade engine Vi 575mm 956 G5	Philips / Signify	
929003978606	InteGrade engine Vi 855mm 956 G5	Philips / Signify	
929003978706	InteGrade engine Vi 1150mm 956 G5	Philips / Signify	
929003978806	InteGrade engine NB Va 140mm WWR G5	Philips / Signify	
929003978906	InteGrade engine NB Va 575mm WWR G5	Philips / Signify	
929003979006	InteGrade engine NB Va 1430mm WWR G5	Philips / Signify	
929003979106	InteGrade engine NB Va 140mm 956 G5	Philips / Signify	
929003979206	InteGrade engine NB Va 575mm 956 G5	Philips / Signify	
929003979306	InteGrade engine NB Va 1430mm 956 G5	Philips / Signify	
929003979406	InteGrade engine NB Va 1150mm WWR G5	Philips / Signify	
929003979506	InteGrade engine NB Va 1570mm WWR G5	Philips / Signify	
929003979606	InteGrade engine UB Va 855mm WWR G5	Philips / Signify	
929003979706	InteGrade engine UB Va 1150mm WWR G5	Philips / Signify	
929003979806	InteGrade engine UB Vi 140mm WWR G5	Philips / Signify	
929003979906	InteGrade engine UB Vi 575mm WWR G5	Philips / Signify	
929003980006	InteGrade engine UB Vi 855mm WWR G5	Philips / Signify	
929003980106	InteGrade engine UB Vi 1150mm WWR G5	Philips / Signify	
929003980206	InteGrade engine UB Vi 1150mm 956 G5	Philips / Signify	
929003980306	InteGrade engine UB Vi 855mm 956 G5	Philips / Signify	
929003980406	InteGrade engine Va 140mm 930 G5 AH	Philips / Signify	
929003980506	InteGrade engine Va 575mm 930 G5 AH	Philips / Signify	
929003980606	InteGrade engine Va 1150mm 930 G5 AH	Philips / Signify	
929003980706	InteGrade engine Va 140mm 930 PW G5	Philips / Signify	
929003980806	InteGrade engine Va 140mm 940 PW G5	Philips / Signify	
929003980906	InteGrade engine Va 575mm 930 PW G5	Philips / Signify	



EU Declaration of Conformity

Document No.: 2025A0124

12NC	Product Description	Brand	Remarks
929003981006	InteGrade engine Va 575mm 940 PW G5	Philips / Signify	
929003981106	InteGrade engine Va 855mm 930 PW G5	Philips / Signify	
929003981206	InteGrade engine Va 855mm 940 PW G5	Philips / Signify	
929003981306	InteGrade engine Va 1150mm 930 PW G5	Philips / Signify	
929003981406	InteGrade engine Va 1150mm 940 PW G5	Philips / Signify	
929003981506	InteGrade engine Vi 140mm 930 PW G5	Philips / Signify	
929003981606	InteGrade engine Vi 140mm 940 PW G5	Philips / Signify	
929003981706	InteGrade engine Vi 575mm 930 PW G5	Philips / Signify	
929003981806	InteGrade engine Vi 575mm 940 PW G5	Philips / Signify	
929003981906	InteGrade engine Vi 855mm 930 PW G5	Philips / Signify	
929003982006	InteGrade engine Vi 855mm 940 PW G5	Philips / Signify	
929003982106	InteGrade engine Vi 1150mm 930 PW G5	Philips / Signify	
929003982206	InteGrade engine Vi 1150mm 940 PW G5	Philips / Signify	
929003982306	InteGrade engine NB Va 140mm 930 PW G5	Philips / Signify	
929003982406	InteGrade engine NB Va 140mm 940 PW G5	Philips / Signify	
929003982506	InteGrade engine NB Va 575mm 930 PW G5	Philips / Signify	
929003982606	InteGrade engine NB Va 575mm 940 PW G5	Philips / Signify	
929003982706	InteGrade engine NB Va 1430mm 930 PW G5	Philips / Signify	
929003982806	InteGrade engine NB Va 1430mm 940 PW G5	Philips / Signify	
929003982906	InteGrade engine NB Va 1150mm 930 PW G5	Philips / Signify	
929003983006	InteGrade engine NB Va 1150mm 940 PW G5	Philips / Signify	
929003983106	InteGrade engine NB Va 1570mm 930 PW G5	Philips / Signify	
929003983206	InteGrade engine NB Va 1570mm 940 PW G5	Philips / Signify	
929003983306	InteGrade engine UB Va 855mm 930 PW G5	Philips / Signify	
929003983406	InteGrade engine UB Va 855mm 940 PW G5	Philips / Signify	
929003983506	InteGrade engine UB Va 1150mm 930 PW G5	Philips / Signify	
929003983606	InteGrade engine UB Va 1150mm 940 PW G5	Philips / Signify	
929003983706	InteGrade engine UB Vi 140mm 930 PW G5	Philips / Signify	
929003983806	InteGrade engine UB Vi 140mm 940 PW G5	Philips / Signify	
929003983906	InteGrade engine UB Vi 575mm 930 PW G5	Philips / Signify	
929003984006	InteGrade engine UB Vi 575mm 940 PW G5	Philips / Signify	
929003984106	InteGrade engine UB Vi 855mm 930 PW G5	Philips / Signify	
929003984206	InteGrade engine UB Vi 855mm 940 PW G5	Philips / Signify	
929003984306	InteGrade engine UB Vi 1150mm 930 PW G5	Philips / Signify	
929003984406	InteGrade engine UB Vi 1150mm 940 PW G5	Philips / Signify	
929003984506	InteGrade engine NB Vi 140mm 930 PW G5	Philips / Signify	
929003984606	InteGrade engine NB Vi 140mm 940 PW G5	Philips / Signify	
929003984706	InteGrade engine NB Vi 1430mm 930 PW G5	Philips / Signify	
929003984806	InteGrade engine NB Vi 1430mm 940 PW G5	Philips / Signify	
929003984906	InteGrade engine NB Vi 575mm 930 PW G5	Philips / Signify	



EU Declaration of Conformity

Document No.: 2025A0124

12NC	Product Description	Brand	Remarks
929003985006	InteGrade engine NB Vi 575mm 940 PW G5	Philips / Signify	
929003985106	InteGrade engine NB Vi 1150mm 930 PW G5	Philips / Signify	
929003985206	InteGrade engine NB Vi 1150mm 940 PW G5	Philips / Signify	
929003985306	InteGrade engine NB Vi 1570mm 930 PW G5	Philips / Signify	
929003985406	InteGrade engine NB Vi 1570mm 940 PW G5	Philips / Signify	
929003985506	InteGrade engine UB Va 1150mm 940 PW G5 HFR	Philips / Signify	
929003985606	InteGrade engine Va 1150mm 940 PW G5 HFR	Philips / Signify	
929003986606	InteGrade engine Va 760mm 940 PW G5	Philips / Signify	
929003986706	InteGrade engine Va 760mm 930 PW G5	Philips / Signify	
929003986806	InteGrade engine Va 760mm 956 G5	Philips / Signify	
929003986906	InteGrade engine Va 760mm WWR G5	Philips / Signify	
929003987006	InteGrade engine NB Va 1660mm 930 PW G5	Philips / Signify	
929003987106	InteGrade engine NB Va 1660mm 940 PW G5	Philips / Signify	
929003987206	InteGrade engine NB Va 1660mm WWR G5	Philips / Signify	
929003987306	InteGrade engine UB Vi 760mm 930 PW G5	Philips / Signify	
929003987406	InteGrade engine UB Vi 760mm 940 PW G5	Philips / Signify	
929003987506	InteGrade engine UB Vi 760mm 956 G5	Philips / Signify	
929003987606	InteGrade engine UB Vi 760mm WWR G5	Philips / Signify	
929003987706	InteGrade engine NB Vi 1660mm 930 PW G5	Philips / Signify	
929003987806	InteGrade engine NB Vi 1660mm 940 PW G5	Philips / Signify	
929003988206	InteGrade engine NB Va 140mm 965 G5	Philips / Signify	
929003988306	InteGrade engine NB Va 1430mm 965 G5	Philips / Signify	
929003988406	InteGrade engine NB Va 760mm 956 G5	Philips / Signify	
929003988506	InteGrade engine NB Va 855mm 956 G5	Philips / Signify	
929003988606	InteGrade engine NB Va 1150mm 956 G5	Philips / Signify	
929003988706	InteGrade engine NB Va 1570mm 956 G5	Philips / Signify	
929003988806	InteGrade engine NB Va 760mm 940 PW G5	Philips / Signify	
929003988906	InteGrade engine NB Va 855mm 940 PW G5	Philips / Signify	
929003989006	InteGrade engine NB Vi 760mm 956 G5	Philips / Signify	
929003989106	InteGrade engine NB Vi 855mm 956 G5	Philips / Signify	
929003989206	InteGrade engine NB Vi 1150mm 956 G5	Philips / Signify	
929003989306	InteGrade engine NB Vi 1430mm 956 G5	Philips / Signify	
929003989406	InteGrade engine NB Vi 1570mm 956 G5	Philips / Signify	
929003989506	InteGrade engine NB Vi 760mm 940 PW G5	Philips / Signify	
929003989606	InteGrade engine NB Vi 855mm 940 PW G5	Philips / Signify	
929003989706	InteGrade engine Va 140mm Rose G5	Philips / Signify	
929003989806	InteGrade engine Va 855mm Rose G5	Philips / Signify	
929003989906	InteGrade engine Va 1150mm Rose G5	Philips / Signify	
929003990006	InteGrade engine NB Va 140mm Rose G5	Philips / Signify	
929003990106	InteGrade engine NB Va 575mm Rose G5	Philips / Signify	



EU Declaration of Conformity

Document No.: 2025A0124

12NC	Product Description	Brand	Remarks
929003990206	InteGrade engine NB Va 1430mm Rose G5	Philips / Signify	
929003990306	InteGrade engine UB Vi 140mm Rose G5	Philips / Signify	
929003990406	InteGrade engine UB Vi 855mm Rose G5	Philips / Signify	
929003990506	InteGrade engine UB Vi 1150mm Rose G5	Philips / Signify	
929003990606	InteGrade engine ECO Va 140mm 930 PW G5	Philips / Signify	
929003990706	InteGrade engine ECO Va 575mm 930 PW G5	Philips / Signify	
929003990806	InteGrade engine ECO Va 760mm 930 PW G5	Philips / Signify	
929003990906	InteGrade engine ECO Va 855mm 930 PW G5	Philips / Signify	
929003991006	InteGrade engine ECO Va 1150mm 930 PW G5	Philips / Signify	
929003991106	InteGrade engine ECO Va 140mm 940 PW G5	Philips / Signify	
929003991206	InteGrade engine ECO Va 575mm 940 PW G5	Philips / Signify	
929003991306	InteGrade engine ECO Va 760mm 940 PW G5	Philips / Signify	
929003991406	InteGrade engine ECO Va 855mm 940 PW G5	Philips / Signify	
929003991506	InteGrade engine ECO Va 1150mm 940 PW G5	Philips / Signify	