
PHILIPS


Installation Instruction


DURALED PRO

Industrial Luminaire



EYEBOLT VERSION (Standard Supply)





MOUNTING BRACKET DETAILS

Dimensions in mm

Type : BY202P Lamp : LED

Wattage/Voltage : 35W / 240 VAC, 50 Hz

IP Classification : IP65

Net Weight : 850 gm Approx

Max. Projected Area : 0.016 m² CCT : 6500K, 4000K

Application : Indoor/ Under coverd area


IP65


ta 45°






All the pictures in the MI sheet are representative only and may vary from the Actual Product.







CAUTION

- 1. Ensure L-N-E is connected in right manner.
- 2. 3 Core cable should be properly connected with ground.
- 3. Product should be operated between 120-270V A.C.
- 4. Luminaire must be brought down from the mounting position for maintenance.
- 5. In case the Diffuser is found broken/damaged luminaire should not be powered on and it has to be replaced before using the luminaire.
- The light source of this luminaire is not replaceable, when the light source reaches its end of life the whole luminaire shall be replaced.
- The external flexible cable or cord of this luminaire cannot be replaced; if the cord is damaged, the Driver shall be replaced.
- 8. Warrant Void if Earthing wire not connected properly with ground.
- 9. Warranty Void if used in outdoor applications

FAILURE OF PRODUCT DUE TO NON COMPLIANCE TO ANY OF THE ABOVE, VOIDS WARRANTY OF PRODUCT.

All the pictures in the MI sheet are representative only and may vary from the Actual Product.

