



EU Declaration of Conformity

Document No.: 2023A0045

Year in which CE Mark was first affixed: 2023

1. Product Range / Model:

Product Range / Model:

NAME: TrustSight Gen3 Plus BASIC, PRO & DALI

DESCRIPTION: Electric source for safety services (ESSS) supplied electronic control gear for emergency lighting (self-contained)

2. Manufacturer Name & Address:

Signify

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

3. This declaration of conformity is issued under the sole responsibility of the manufacturer.

4. Object of the declaration:

Product Code:

See for Unique product ID number of all products under the family described above Annex: Specification of the products

5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Low Voltage Directive (LVD), 2014/35/EU

- EN 61347-1:2015+ A1:2021
- EN 61347-2-7:2012+A1:2019+A2:2022
- EN 61347-2-13: 2014 + A1:2017

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN IEC 55015:2019+A11:2020
- EN IEC 61000-3-2:2019+A1:2021
- EN 61000-3-3:2013+A1:2019+A2:2021
- EN IEC 61547:2009

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- Commission Regulation (EU) 2019/2020 Article and amendment Commission Regulation (EU) 2021/341

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN IEC 63000:2018

7. Additional information: The product(s) in this declaration is/are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Signed for and on behalf of:

19-10-2023

High Tech Campus 48

5656 AE Eindhoven, The Netherlands

Ms C Sweegers

Regulatory Affairs Manager LED Electronics





EU Declaration of Conformity

Document No.: 2023A0045

Specification of the products:

10NC	12NC	Product Description: TrustSight drivers	Brand
9290 034 186	9290 034 18606	TrustSight BASIC 15-55V NiMH+	Philips
9290 034 185	9290 034 18506	TrustSight BASIC 45-300V NiMH+	Philips
9290 034 184	9290 034 18406	TrustSight PRO 15-55V NiMH+	Philips
9290 034 189	9290 034 18906	TrustSight PRO 45-300V NiMH+	Philips
9290 034 188	9290 034 18806	TrustSight DALI 15-55V NiMH+	Philips
9290 034 187	9290 034 18706	TrustSight DALI 45-300V NiMH+	Philips
9290 034183	9290 034 18306	TrustSight BASIC 15-55V LFP+	Philips
9290 034182	9290 034 18206	TrustSight BASIC 45-300V LFP+	Philips
9290 034 181	9290 034 18106	TrustSight PRO 15-55V LFP+	Philips
9290 034 180	9290 034 18006	TrustSight PRO 45-300V LFP+	Philips
9290 034 179	9290 034 17906	TrustSight DALI 15-55V LFP+	Philips
9290 034 178	9290 034 17806	TrustSight DALI 45-300V LFP+	Philips

10NC	12NC	Product Description: TrustSight batteries	Brand
9290 016 525	9290 016 52506	TrustSight 3.6V 3cell 4000mAh batt NiMH	Philips
9290 016 526	9290 016 52606	TrustSight 4.8V 4cell 4000mAh batt NiMH	Philips
9290 016 527	9290 016 52706	TrustSight 6.0V 5cell 4000mAh batt NiMH	Philips
9290 034 192	9290 034 19206	TrustSight 3.2V 3cell 4500mAh batt LFP+	Philips
9290 034 191	9290 034 19106	TrustSight 6.4V 4cell 3000mAh batt LFP+	Philips
9290 034 232	9290 034 23206	TrustSight 6.4V 4cell 3000mAh LFP+ FRC	Philips

10NC	12NC	Product Description: TrustSight accessories	Brand
9290 016 533	9290 016 53306	TrustSight Strain Relief	Philips
9290 016 534	9290 016 53406	TrustSight Battery Independent box	Philips
9290 016 536	9290 016 53606	TrustSight LED Indicator	Philips
9290 021 706	9290 021 70606	TrustSight High Brightness LED Indicator	Philips
9290 016 822	9290 016 82206	TrustSight Battery Harness NiMH	Philips
9290 034 194	9290 034 19406	TrustSight Battery Harness LFP+	Philips
9290 034 235	9290 034 23506	TrustSight Battery Harness LFP FRC+	Philips