


Wide Batten BN005C



Mounting Instruction/Petunjuk Instalasi/Hướng dẫn lắp đặt/คู่มือการติดตั้ง/تعليمات التركيب

VI.0



Product Description	Power	Input Voltage	Frequency	Energy efficiency class of light source	Dimension (LxWxH)	A	kg
BN005C LED22/WW L600 PSU GM	20	220-240V~	50/60Hz	D	600x70x27mm	255-385mm	0.145
BN005C LED22/NW L600 PSU GM	20	220-240V~	50/60Hz	D	600x70x27mm	255-385mm	0.145
BN005C LED22/CW L600 PSU GM	20	220-240V~	50/60Hz	D	600x70x27mm	255-385mm	0.145
BN005C LED40/WW L1200 PSU GM	40	220-240V~	50/60Hz	E	1200x70x27mm	400-600mm	0.250
BN005C LED40/NW L1200 PSU GM	40	220-240V~	50/60Hz	D	1200x70x27mm	400-600mm	0.250
BN005C LED40/CW L1200 PSU GM	40	220-240V~	50/60Hz	D	1200x70x27mm	400-600mm	0.250

