

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: PHILIPS

Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

Model identifier: 929003949301

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	NA		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	-
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	Yes


Product parameters

Parameter	Value	Parameter	Value
General product parameters:			
Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	26	Energy efficiency class	E
Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	3 345 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000
On-mode power (P_{on}), expressed in W	26,0	Standby power (P_{sb}), expressed in W and rounded to the second decimal	0,00
Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	90
Outer dimensions without separate control gear, lighting control	Height	2	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	20	
	Depth	24	
			See image in last page

parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,422 0,386
Parameters for LED and OLED light sources:			
R9 colour rendering index value	70	Survival factor	0,90
the lumen maintenance factor	0,96		

(a) : not applicable;

(b) : not applicable;



Model placed on the Union market from 20/03/2025.



EPREL registration number: 2270340

<https://eprel.ec.europa.eu/qr/2270340>

Supplier: Signify Netherlands B.V. (Manufacturer)

Website: www.signify.com

Customer care service:

Name: Customer Care Philips

Website: www.philips.com/lighting

Email: EPREL.PhilipsLighting@Signify.com

Phone: 00800 744 547 75

Address:

I.B.R.S./C.C.R.I. /Numéro 10461
5600VB Eindhoven
Netherlands