

FlexCove G6 Accessory/ LED柔性灯带



Mounting instruction/ 安装说明





Type 型号	Size 尺寸			Housing appearance 外观	kg
	A (mm)	B (mm)	C (mm)		
AC170Z surface mount triangle L1000 G2	20	20	1000	E	0.202
AC170Z surface mount High H L1000 G2	17	14.6	1000	F	0.187
AC170Z surface mount Low H L1000 G2	17	8	1000	G	0.13
AC170Z recessed High H L1000 G2	25	14.6	1000	H	0.215
AC170Z recessed Low H L1000 G2	24	8	1000	I	0.153
AC170Z mounting accessory PRO	12.6	5.6	1000	J	0.082

E


Housing Size
型材尺寸




Diffuser size
面罩尺寸



End Cap size
配套堵头尺寸




Clip size
卡扣尺寸




Unit单位: mm毫米

F


Housing Size
型材尺寸




Diffuser size
面罩尺寸



End Cap size
配套堵头尺寸



Clip size
卡扣尺寸



Unit单位: mm毫米

Signify Luminares (Shanghai) Co., Ltd.
Address: 2F, Building 1, No. 2555 Hechuan Road, Minhang District, Shanghai
Postalcode: 200233


昕诺飞灯具(上海)有限公司
地址: 上海市闵行区合川路2555号1幢二楼
邮编: 200233

PHILIPS


Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

G


Housing Size
型材尺寸




Diffuser size
面罩尺寸



End Cap size
配套堵头尺寸




Clip size
卡扣尺寸




Unit unit: mm毫米

H


Housing Size
型材尺寸




Diffuser size
面罩尺寸



End Cap size
配套堵头尺寸




Clip size
卡扣尺寸




Unit unit: mm毫米

I


Housing Size
型材尺寸




Diffuser size
面罩尺寸



End Cap size
配套堵头尺寸




Clip size
卡扣尺寸



Unit unit: mm毫米

J


Housing Size
型材尺寸



Unit unit: mm毫米

IP20 version IP20版本


1 Detach the entire tape
剥掉胶带



1.a Paste the tape into the profile
将灯带粘贴在型材内




2 Cover the housing with diffuser
将铝材盖上面罩



3 Cover the end plug
盖上堵头




4 Fix the clip on the wall with screws
用螺丝将卡扣固定在墙上



Surface series installation method: Fix the clip on a flat wall
表面系列安装方式: 将卡扣固定在平面的墙上


Recessed series installation method: Dig a groove in the wall and fix the clip in the groove.
嵌入式安装方式: 将墙面开槽, 把卡扣固定在槽里



Note:


Type 型号	Groove depth range 开槽深度范围
AC170Z recessed Low H L11000	6.0-7.5mm
AC170Z recessed High H L11000	14.0-15.0mm

5 Install the housing into the clip
将铝材装进卡扣



Surface series installation method: Surface series installation method:
表面系列安装方式: 表面系列安装方式:

Recessed series installation method: Recessed series installation method:
嵌入式安装方式: 嵌入式安装方式:



⚠ Note: If IP65 Flexcove to be used with accessories, please raise ETO request to add 3M adhesive tape on the product.
注意: IP65 LED柔性灯带和型材配合使用, 需要灯带增加3M背胶, 请联系ETO部门。

Please read this manual carefully before using the product
使用本产品前，请先仔细阅读本手册



- The manufacturer will not be held responsible for improper usage or modifications of the product.
所有不当使用或自行更改产品结构而导致损坏，生产商不负任何责任。
- Recommend to use Philips power supply (This product must use SELV (isolated) power supply). The power supply must comply with independent driver requirements of IEC61347-2-13/GB19510.14.
推荐同飞利浦电源驱动器配套使用（产品必须和SELV隔离电源一起使用）。电源驱动器必须符合IEC61347-2-13/GB19510.14的独立式要求。
- This product must use Philips connectors.
此产品必须使用飞利浦连接器。
- Indoor use only. Do not stare at the product when the lights is on.
仅限室内使用，灯具在使用时请不要直视光源。
- The light source of this product is not replaceable; when the light source reaches its end of life the whole luminaire shall be replaced.
灯具的光源不可单独替代，当光源寿终时，整个灯具需要被替换掉。
- Please take static proof measures when installing and maintaining the product.
安装和维护灯具时，请做好防静电措施。
- In case of operation failure, please switch off the power and contact your near -est dealer.
如发现异常或操作有任何问题，请务必先切断电源，然后与经销商联系。

Maintenance 保养方法:

- In order to ensure optimum performance, please clean the product regularly(recommended once a year). When cleaning the product, please use soft dry cotton cloth only.
为了保持灯带明亮效果，请定期（一年一次）时行清洁。灯带不洁处需擦拭时请用柔软干燥的布料擦拭。



Attention 注意:

- Don't use chemical solvents to clean the product.
请不要用香蕉水等挥发性物质擦拭灯带表面，请不要对灯具喷洒任何化学药剂，否则灯具可能会变色或损坏。
- Please switch off the power supply before mounting and maintaining this product.
安装和维护灯带时，请务必先关闭电源！
- The lighting strip shall be installed by a qualified electrician and wired in accordance with the latest IEE regulations or the national requirements.
灯带应由有资格的电工安装，接线符合IEE电气标准或国家标准。
- The product shall not be covered with thermal insulation or similar material under any circumstances.
灯带不允许被隔热或类似材料覆盖。
- The product should not be used in directly exposed environment containing hazardous substances to silicone rubber. Consult your local dealer for use in any special applications.
灯带不得用于直接暴露在硅胶有害的环境中。如用于特定场合请咨询当地经销商。
- The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc must be avoided during the use and storage.
灯具避免在腐蚀性环境或含有有害物质，例如硫化物，卤化物，邻苯二甲酸酯等环境中存储和使用。
- The external flexible cable or cord of this product cannot be replaced; if the cord is damaged, the product shall be destroyed.
不能替换此灯具的外部柔性电缆或电线，如果电缆损坏，整个灯具需要处理掉。
- Do not turn the lamp belt on.
请勿将灯带盘起点亮。

有害物质清单/Harmful Substance Form



This marking indicates that this product should not be disposed with other household wastes throughout the EU. To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.

产品中有害物质的名称及含量

部件名称	有害物质					
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr ⁶⁺)	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
LED灯板/光源	○	○	○	○	○	○
驱动器(板), 铜 轴及电子零部件	×	○	○	○	○	○
透镜光学部件	○	○	○	○	○	○
外壳及 其它零部件	○	○	○	○	○	○

本表格依据SJT/T 11364的规定编制
 ○ 表示该有害物质在该部件所有均质材料中的含量均在GB/T 26572规定的限量要求以下。
 × 表示该有害物质至少在该部件的某一均质材料中的含量超出GB/T 26572规定的限量要求。

Applicable to China Only