



PureForm P26 Gen 2		PureForm P26 Gen 1		PureForm P34 Gen 1		PowerForm Gen 2	
Selection	Nom. Lumens	Selection	Nom. Lumens	Selection	Nom. Lumens	Selection	Nom. Lumens
A01	12,000	48L-500	11,000				
A02	15,500	48L-700	15,000				
A03	18,000	64L-600	17,000				
A04	22,000	64L-800	22,000				
A05	25,000	80L-700	24,000				
A06	28,000	80L-800	27,000	96L-800	30,000		
A07	32,500	80L-900	29,000	96L-900	34,000		
A08	36,000			96L-1050	38,000	92L-900	36,000
A09	40,000					92L-1A	41,000
A10	44,000			128L-900	45,000	138L-900	45,000
A11	50,000			128L-1050	50,000		
A12	57,000					138L-1A	55,000
A13	62,000					184L-900	62,000
						184L-1A	73,000