GreenUp Spotlight


RS078B

Mounting instructions / Petunjuk Pemasangan

CB | IEC 60598 | Ta 25°C | Max. 40°C Min. -20°C | IP20 | CRI ≥90


Product model Model Produk	Power Daya	Voltage Tegangan	Frequency Frekuensi	PF	CCT	Beam Angle Sudut kemiringan	kg
RS078B P9	9W	220-240V	50/60Hz	0.5	3000K/4000K	24°/38°	0.154
RS078B P11	11W					24°	0.184
RS078B P15	15W						0.319

1




Product model Model Produk	Cut out size Ukuran lubang potong (mm)	A (mm)	B (mm)	Ceiling thickness ketebalan plafon (mm)
RS078B P9	D75	85	62	*7-15
RS078B P11	D75	85	70	*7-15
RS078B P15	D95	105	85	*7-15


*To install onto a ceiling thickness of 7-15mm, a specific cut-out size is required,and the opening shall not be too large to hold the luminaire.
Untuk pemasangan pada plafon dengan ketebalan 7–15 mm, diperlukan ukuran lubang pemasangan yang sesuai. Lubang tidak boleh terlalu besar agar lampu dapat terpasang dengan kuat dan tidak mudah lepas.



2 2.1




2.2




2.3 Suggestion Supply Power Cable
Rekomendasi kabel listrik

5-8 mm²




60227 IEC52 2×0.75 mm²
L:Brown/ Cokelat
N:Blue/ Biru
2×0.75 mm²

2.4 Connect Power Supply Cable
Hubungkan Kabel




Remark: Please insert the cable into terminal block,then pull the cable lightly to make sure the cable is fixed by the terminal block.
Catatan: Masukkan kabel ke dalam blok terminal dan kencangkan sekrup, pastikan kabel terpasang kuat.

3 3.1




3.2




Signify Luminaires (Shanghai) Co., Ltd.
Address: 2F, Building 1, No. 2555 Hechuan Road, Minhang District, Shanghai, P.R. China
Postalcode: 200233

PHILIPS
Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V

3.3



3.4




After the luminaire installed, please tear off the protective film.
Setelah lampu terpasang, lepas lapisan pelindungnya.


4




5




Please do not use the following methods to install luminaires:
Hindari cara pemasangan lampu berikut:






When the light is lit, do not touch the light head directly with your hands.
Dilarang menyentuh bagian kepala lampu secara langsung saat lampu menyala



After turning off the power and 15-minute cooling-off, you can proceed operations with your hands.
Pastikan lampu mati dan biarkan dingin selama 15 menit sebelum menyentuh kepala lampu dengan tangan



Product model/ Model Produk	Power/ Daya (W)	Operating current/ Operasi (A) (@220V)	Inrush current/ Arus masuk (A)	Inrush current duration/ T(@50% of Ipeak) (µs)	Leakage current/ Kebocoran arus (mA)	The 16A Type B miniature circuit breaker can be connected to up to the number of luminaires Kapasitas maksimum jumlah lampu untuk **MCB 16A Tipe B** (pcs)	The 16A C miniature circuit breaker can connect up to the number of luminaires Kapasitas maksimum jumlah lampu untuk **MCB 16A Tipe C** (pcs)
RS078B P9	9W	0.067	1.52	30	0.7	408	408
RS078B P11	11W	0.078	9.44	78	0.7	190	318
RS078B P15	15W	0.112	8.2	22	0.7	245	245

01.Luminaires should be installed by qualified electricians, and the wiring should comply with IEE electrical standards or national standards.
02.This luminaire is not suitable to be installed with thermal-insulated pads or similar materials.
03.Power off during installation and wiring connection.
04.The light source and/or control devices in this luminaire may only be replaced by the manufacturer or its service agent or a person of similar qualifications.
05.Lamps should not be stored and used in corrosive environments or environments containing harmful substances, such as, sulfides,l halides, phthalates, etc.
06.This luminaire is for indoor use only.
07.The ingress protection of this product is IP20, it is strongly recommended to check the application environment beforel installation to prevent possible water ingress.Water ingress may cause possible electrical failures, even safety incidences, which are not covered in Philips/Signify warranty.
08.No hot-plug or live operation. Do not touch the light head or any heated parts during the light on.
09.Choose right installation position, prevent less than 1.3m long-time staring on the luminaire.
10.The manufacturer shall not be liable for damage caused by improper use or self-alteration of the product structure.
11.If the external cord or cord of this luminaire is damaged, the cord should be replaced by the manufacturer or its service agent or a person with similar qualifications to avoid danger.

01.Luminer harus dipasang oleh teknisi listrik, dan kabel harus mematuhi standar kelistrikan IEE atau standar nasional.
02.luminer tidak cocok untuk menutupi dengan bantalan isolasi termal atau bahan serupa.
03.Jangan memberi energi selama pengkabelan.
04.Sumber cahaya dan / atau perangkat kontrol dalam luminer ini hanya dapat diganti oleh produsen atau agen servisnya atau seseorang dari quali_cations serupa.
05.Lampu tidak boleh disimpan dan digunakan di lingkungan korosif atau lingkungan yang mengandung zat berbahaya seperti sul_des,halida, ftalat, dll.
06.luminer hanya untuk penggunaan di dalam ruangan.
07.tingkat perlindungan produk ini adalah IP20, tidak dapat mencegah masuknya air, sangat disarankan untuk memeriksa dan mengevaluasi kemampuan beradaptasi lingkungan penggunaan sebelum menginstal produk ini. Setelah ada masuknya air, produk mungkin memiliki listrik kegagalan atau kecelakaan keselamatan, dan Philips/ Signify tidak bertanggung jawab atas garansi ini.
08.Jika catu daya mulai memanas, operasi berlangsung jangan menyentuh sumber cahaya atau bagian yang dipanaskan, dll.
09.Posisi pemasangan luminer tidak boleh terlalu dekat pada jarak kurang dari l,3m untuk waktu yang lama.
10.Produsen tidak bertanggung jawab atas kerusakan yang disebabkan oleh penggunaan yang tidak tepat atau perubahan dari struktur produk dengan sendirinya.
11.Jika kabel eksternal atau kabel luminer ini rusak, kabel harus diganti oleh pabrikan atau agen servisnya atau seseorang dengan kualifikasi serupa untuk menghindari bahaya.