

PHILIPS

InteGrade

LED

InteGrade accessories



Datasheet

InteGrade LED system

Compact linear LED lighting for ultimate shopping experience

Thanks to a range of accessories, engine lengths, fixtures, color temperatures and Constant Voltage LED power drivers, the InteGrade LED system offers modular approach for maximum design flexibility. This enables a vast variety of innovative systems with style and functionality according the needs of the stores. The accessory table shows which accessories are suitable for your InteGrade LED system.

January 2024



Ordering data

Commercial product name	EOC	12NC	Box quantity
InteGrade power cable 1m(39") black	8718291 218128 00	9290 006 41014	24
InteGrade power cable 2.5m(98") black	8718291 221449 00	9290 006 41114	24
InteGrade cable 1m(39") black angle	8718291 221364 00	9290 006 44614	24
InteGrade cable 2.5m(98") black angle	8718291 221463 00	9290 006 44814	24
InteGrade power cable 1m(39") white	8718291 221401 00	9290 006 45614	24
InteGrade power cable 2.5m(98") white	8718291 221487 00	9290 006 44514	24
InteGrade cable 1m(39") white angle	8718291 221425 00	9290 006 44714	24
InteGrade cable 2.5m(98") white angle	8718291 221500 00	9290 006 44914	24
InteGrade power cable 6m white	8718696 824375 00	9290 016 24806	12
InteGrade power cable 6m black	8719514 294943 00	9290 028 59106	12
InteGrade power cable 1.85m white	8718696 824450 00	9290 016 25206	96
InteGrade spacer cable 0.5m black	8718291 221524 00	9290 006 45014	24
InteGrade spacer cable 0.5m white	8718291 221548 00	9290 006 45114	24
InteGrade spacer cable M 0.7m 5.5c black	8718696 824351 00	9290 016 24706	24
InteGrade spacer cable 0.3m black	8718696 824412 00	9290 016 25006	24
InteGrade spacer cable 113mm white	8718696 824436 00	9290 016 25106	24
InteGrade spacer cable 0.2m T s-s	8719514 281141 00	9290 021 82106	24
InteGrade magnet for M style profile	9718291 707271 00	9290 008 71413	100
InteGrade mounting clip under shelf	8718291 218814 00	9290 006 43903	100
InteGrade mounting clip for T style prof	8718291 676508 00	9290 008 53213	100
InteGrade snap-in clip for fixtures	8719514 281325 00	9290 021 99706	100
InteGrade screw clip_Tstyle prof and fix	8719514 281356 00	9290 021 99806	100
InteGrade engine mounting clip G2	9718696 657126 00	9290 015 16106	100
InteGrade mounting clip canopy	8718696 716304 00	9290 015 71106	100
InteGrade engine clip mullion center	8718696 824535 00	9290 016 24406	100
InteGrade engine clip mullion side	8718696 824559 00	9290 016 24506	100
InteGrade engine clip magnetic	8718696 824573 00	9290 016 24606	100
InteGrade profile 875mm(34")	8718291 219538 00	9290 006 43413	48
InteGrade profile 1175mm(46")	8718291 219552 00	9290 006 43313	48
InteGrade profile 2000mm(79")	8718291 257899 00	9290 006 54413	48
InteGrade profile 2000mm(79") F style	8718291 227892 00	9290 006 54313	24
InteGrade profile 2000mm(79") T style CTR	8718291 676461 00	9290 008 53013	16
InteGrade profile 2000mm(79") T style SD	8718291 676485 00	9290 008 53113	16
InteGrade prof 2000mm T style CTR G2	8719514 281387 00	9290 021 99506	16
InteGrade prof 2000mm T style SD G2	8719514 281400 00	9290 021 99606	16
InteGrade connector	8718696 462157 00	9290 009 59106	500
InteGrade engine lock inline	8718291 219514 00	9290 006 43713	100
InteGrade rotational bracket	8718291 707691 00	9290 008 74613	100

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _a (ambient temperature)	0	0	30	°C


* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Mechanical characteristics

Parameter	Min	Typ	Max	Unit
-----------	-----	-----	-----	------



Absolute ratings

Parameter	Min	Max	Unit
Ambient temperature	-30	30	°C
Storage temperature	-30	60	°C

Application information

Certificates and Standards

Application	
Dimming	Yes



© 2024 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

15/01/2024