

PHILIPS

InteGrade

LED

InteGrade S accessories



Datasheet

InteGrade S LED system

January 2024



indirect



instant

Ordering data

Commercial product name	EOC	12NC	Box quantity
InteGrade S mounting clip	8718699 711443 00	9290 021 32106	100
InteGrade S mounting profile 900mm	8718699 711481 00	9290 021 32306	12
InteGrade S mounting profile 1200mm	8718699 711504 00	9290 021 32406	12

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _a (ambient temperature)	0	0	30	°C


* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Mechanical characteristics

Parameter	Min	Typ	Max	Unit
-----------	-----	-----	-----	------



Absolute ratings

Parameter	Min	Max	Unit
Ambient temperature	-30	30	°C
Storage temperature	-30	60	°C

Application information

Certificates and Standards

Application	
Dimming	Yes



© 2024 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

15/01/2024