



Small in size, big in quality

TrueFashion EM

TrueFashion is the LED projector family answering miniaturization and presentation needs of specialized retailers. Firstly, these miniaturized spots with clean and fine detailing offer contemporary design and blend seamlessly into your store interior for a tailor-made look. Secondly, it provides high quality accentuation effect thanks to its innovative OptiAccent lens technology (FPO), which provides higher central intensity beam without spill light to maximize the contrast ratio hence optimize the accent effect. Especially in challenging narrow spot (12D) and spot (18D) applications, the difference of OptiAccent to Chip on Board and reflector optics is like day and night. OptiAccent also reduces direct glare by a factor of 5 to enable superior visual comfort. Lastly, TrueFashion also has the light spectra taken care of: the specially designed Philips LED flavors enhance colors (saturation) and whites, while offering high degree of fidelity (exceeds CRI90). This is how TrueFashion ensures a superior light experience in your retail applications.

Benefits

- High-impact and dramatic accentuation effect
- Unobtrusive and flexible lighting installation
- Bright whites, crisp blacks, vibrant colors
- Increased visual comfort

TrueFashion EM

Features

- Miniaturized spot head in the diameter of 66mm for the Mini and 80mm for the Compact size
- OptiAccent (FPO) Lens technology for maximizing central intensity (up to 40%), eliminating spill light/halo in compared to a traditional Chip-On Board LED and reflector optical system, hence offering high contrast accentuation as opposed to a flat and vague light effect (in Compact only)
- Philips LED flavors: Premium White and Premium Color, CRI exceeds 90 and 3000K (ask your sales contact for different requests)
- Smooth powder coated White or Black paint finish (ask your sales contact for different requests)
- Extra narrow beam spot of 6° with 64K Candela central beam
- Full range of beam spread: 6° / 12° /18° /24° /30° /36° (6° in TrueFashion Highlight, and 12°,24°,36° in Compact only)

Application

- Fashion
- Retail
- Hospitality
- Food and Large Retailers

Warnings and Safety

- The luminaire should be mounted outside of arm's reach
- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements

Versions



RS700B LED10 LED20 BK



RTP-OF-RS700B-TrueFashion-EM



RS700B LED30 LED40 BK



RTP-OF-ST700T-TrueFashion-EM



RTP-OF-GD700B-TrueFashion-EM



RTP-OF-GD700B-TrueFashion-EM



GD700B 1 head BK



RTP-OF-GD700B-TrueFashion-EM

TrueFashion EM

Versions









RTP-OF-RS700B-TrueFashion-EM


GD700B 2 heads WH

GD700B 2 heads BK

Dimensional drawing



Dimensional drawing



| General Information | |
|-------------------------------------|-----------------|
| Driver included | Yes |
| Operating and Electrical | |
| Protection class IEC | Safety class II |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Controls and Dimming | |
| Dimmable | - |
| Mechanical and Housing | |
| Optical cover type | Lens |
| Mech. impact protection code | IK03 |
| Ingress protection code | IP20 |
| Approval and Application | |
| CE mark | Yes |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | -10% / +10% |

Light Technical

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|--|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401548646 | RS700B P21 LED21 930PW PSU NB BK | 3000 K | 90 | 101 lm/W | 2,147 lm |
| 911401547446 | RS700B P40 LED44 930PW PSU WB WH | 3000 K | 90 | 109 lm/W | 4,421 lm |
| 911401547646 | RS700B P40 LED46 930PW PSU MB BK | 3000 K | 90 | 114 lm/W | 4,596 lm |
| 911401546246 | ST700T P21 LED22 830 PSU WB 1C WH | 2700 K | 80 | 104 lm/W | 2,177 lm |
| 911401549046 | GD700B P30 LED33 930PC PSU WB WH | 3000 K | 90 | 109 lm/W | 3,347 lm |
| 911401549146 | GD700B P21 LED14 940PW PSU MB WH HB | 4000 K | 90 | 68 lm/W | 1,432 lm |
| 911401549246 | GD700B P21 LED21 930PW PSU MB WH | 3000 K | 90 | 101 lm/W | 2,147 lm |
| 911401549646 | GD700B P8 LED10 830 PSU MB WH | 3000 K | 80 | 126 lm/W | 1,030 lm |
| 911401550246 | GD700B P42 2XLED21 930PW PSU MB BK | 3000 K | 90 | 101 lm/W | 4,295 lm |
| 911401549546 | GD700B P21 LED21 930PW PSU MB BK | 3000 K | 90 | 101 lm/W | 2,147 lm |
| 911401549746 | GD700B P8 LED10 830 PSU MB BK | 3000 K | 80 | 126 lm/W | 1,030 lm |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|--|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401547346 | RS700B P40 LED47 940PW PSU MB WH | 4000 K | 90 | 118 lm/W | 4,736 lm |
| 911401547546 | RS700B P40 LED46 930PW PSU MB WH | 3000 K | 90 | 114 lm/W | 4,596 lm |
| 911401547746 | RS700B P40 LED43 930PC PSU MB WH | 3000 K | 90 | 106 lm/W | 4,282 lm |
| 911401547846 | RS700B P30 LED37 940PW PSU MB WH | 4000 K | 90 | 122 lm/W | 3,756 lm |
| 911401547946 | RS700B P30 LED36 930PW PSU WB WH | 3000 K | 90 | 117 lm/W | 3,600 lm |
| 911401548146 | RS700B P30 LED36 930PW PSU MB WH | 3000 K | 90 | 118 lm/W | 3,645 lm |
| 911401548246 | RS700B P30 LED34 930PC PSU MB WH | 3000 K | 90 | 110 lm/W | 3,389 lm |
| 911401550046 | GD700B P42 2XLED21 930PW PSU MB WH | 3000 K | 90 | 101 lm/W | 4,295 lm |
| 911401548346 | RS700B P21 LED22 940PW PSU MB WH | 4000 K | 90 | 104 lm/W | 2,213 lm |
| 911401548446 | RS700B P21 LED20 930PW PSU WB WH | 3000 K | 90 | 96 lm/W | 2,021 lm |
| 911401548746 | RS700B P21 LED21 930PW PSU MB WH | 3000 K | 90 | 101 lm/W | 2,147 lm |
| 911401548846 | RS700B P21 LED20 930PC PSU MB WH | 3000 K | 90 | 94 lm/W | 1,997 lm |
| 911401548946 | RS700B P8 LED10 830 PSU WB WH | 3000 K | 80 | 118 lm/W | 969 lm |
| 911401550546 | RS700B P8 LED10 830 PSU MB WH | 3000 K | 80 | 125 lm/W | 1,029 lm |
| 911401548046 | RS700B P30 LED36 930PW PSU WB BK | 3000 K | 90 | 117 lm/W | 3,600 lm |
| 911401542646 | ST700T P41 LED41 930PC PSU WB 1C WH | 3000 K | 90 | 100 lm/W | 4,120 lm |
| 911401542946 | ST700T P41 LED41 930PC PSU WB 1C BK | 3000 K | 90 | 100 lm/W | 4,120 lm |
| 911401543146 | ST700T P41 LED43 930PC PSU MB 1C WH | 3000 K | 90 | 104 lm/W | 4,282 lm |
| 911401543246 | ST700T P41 LED43 930PC PSU MB 1C BK | 3000 K | 90 | 104 lm/W | 4,282 lm |
| 911401544346 | ST700T P35 LED37 930PC PSU WB 1C WH | 3000 K | 90 | 105 lm/W | 3,699 lm |
| 911401544746 | ST700T P35 LED37 930PC PSU MB 1C WH | 3000 K | 90 | 106 lm/W | 3,746 lm |
| 911401544946 | ST700T P35 LED37 930PC PSU MB 1C BK | 3000 K | 90 | 106 lm/W | 3,746 lm |
| 911401545146 | ST700T P21 LED19 930PC PSU WB 1C WH | 3000 K | 90 | 91 lm/W | 1,913 lm |
| 911401545346 | ST700T P21 LED19 930PC PSU WB 1C BK | 3000 K | 90 | 91 lm/W | 1,913 lm |
| 911401545546 | ST700T P21 LED20 930PC PSU NB 1C WH | 3000 K | 90 | 96 lm/W | 2,032 lm |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|--|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401545646 | ST700T P21 LED20 930PC PSU NB 1C BK | 3000 K | 90 | 96 lm/W | 2,032 lm |
| 911401545946 | ST700T P21 LED20 930PC PSU MB 1C WH | 3000 K | 90 | 96 lm/W | 2,032 lm |
| 911401546046 | ST700T P21 LED13 930PC PSU MB 1C BK HB | 3000 K | 90 | 62 lm/W | 1,315 lm |
| 911401546146 | ST700T P21 LED20 930PC PSU MB 1C BK | 3000 K | 90 | 96 lm/W | 2,032 lm |
| 911401546446 | ST700T P21 LED22 830 PSU WB 1C BK | 4000 K | 80 | 104 lm/W | 2,177 lm |
| 911401546946 | ST700T P10 LED12 830 PSU WB 1C WH | 3000 K | 80 | 118 lm/W | 1,186 lm |
| 911401547046 | ST700T P10 LED12 830 PSU WB 1C BK | 4000 K | 80 | 118 lm/W | 1,186 lm |
| 911401547146 | ST700T P10 LED12 830 PSU MB 1C WH | 2700 K | 80 | 125 lm/W | 1,260 lm |
| 911401547246 | ST700T P10 LED12 830 PSU MB 1C BK | 3000 K | 80 | 125 lm/W | 1,260 lm |
| 911401550346 | GD700B P16 2XLED10 830 PSU MB WH | 3000 K | 80 | 125 lm/W | 2,059 lm |
| 911401550446 | GD700B P16 2XLED10 830 PSU MB BK | 3000 K | 80 | 125 lm/W | 2,059 lm |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Order Code | Full Product Name | Power Consumption |
|--------------|-------------------------------------|-------------------|--------------|--|-------------------|
| 911401548646 | RS700B P21 LED21 930PW PSU NB BK | 21.2 W | 911401550546 | RS700B P8 LED10 830 PSU MB WH | 8.2 W |
| 911401547446 | RS700B P40 LED44 930PW PSU WB WH | 40.3 W | 911401548046 | RS700B P30 LED36 930PW PSU WB BK | 30.8 W |
| 911401547646 | RS700B P40 LED46 930PW PSU MB BK | 40.3 W | 911401542646 | ST700T P41 LED41 930PC PSU WB 1C WH | 41.2 W |
| 911401546246 | ST700T P21 LED22 830 PSU WB 1C WH | 21 W | 911401542946 | ST700T P41 LED41 930PC PSU WB 1C BK | 41.2 W |
| 911401549046 | GD700B P30 LED33 930PC PSU WB WH | 30.8 W | 911401543146 | ST700T P41 LED43 930PC PSU MB 1C WH | 41.2 W |
| 911401549146 | GD700B P21 LED14 940PW PSU MB WH HB | 21.2 W | 911401543246 | ST700T P41 LED43 930PC PSU MB 1C BK | 41.2 W |
| 911401549246 | GD700B P21 LED21 930PW PSU MB WH | 21.2 W | 911401544346 | ST700T P35 LED37 930PC PSU WB 1C WH | 35.4 W |
| 911401549646 | GD700B P8 LED10 830 PSU MB WH | 8.2 W | 911401544746 | ST700T P35 LED37 930PC PSU MB 1C WH | 35.4 W |
| 911401550246 | GD700B P42 2XLED21 930PW PSU MB BK | 42.4 W | 911401544946 | ST700T P35 LED37 930PC PSU MB 1C BK | 35.4 W |
| 911401549546 | GD700B P21 LED21 930PW PSU MB BK | 21.2 W | 911401545146 | ST700T P21 LED19 930PC PSU WB 1C WH | 21 W |
| 911401549746 | GD700B P8 LED10 830 PSU MB BK | 8.2 W | 911401545346 | ST700T P21 LED19 930PC PSU WB 1C BK | 21 W |
| 911401547346 | RS700B P40 LED47 940PW PSU MB WH | 40.3 W | 911401545546 | ST700T P21 LED20 930PC PSU NB 1C WH | 21 W |
| 911401547546 | RS700B P40 LED46 930PW PSU MB WH | 40.3 W | 911401545646 | ST700T P21 LED20 930PC PSU NB 1C BK | 21 W |
| 911401547746 | RS700B P40 LED43 930PC PSU MB WH | 40.3 W | 911401545946 | ST700T P21 LED20 930PC PSU MB 1C WH | 21 W |
| 911401547846 | RS700B P30 LED37 940PW PSU MB WH | 30.8 W | 911401546046 | ST700T P21 LED13 930PC PSU MB 1C BK HB | 21 W |
| 911401547946 | RS700B P30 LED36 930PW PSU WB WH | 30.8 W | 911401546146 | ST700T P21 LED20 930PC PSU MB 1C BK | 21 W |
| 911401548146 | RS700B P30 LED36 930PW PSU MB WH | 30.8 W | 911401546446 | ST700T P21 LED22 830 PSU WB 1C BK | 21 W |
| 911401548246 | RS700B P30 LED34 930PC PSU MB WH | 30.8 W | 911401546946 | ST700T P10 LED12 830 PSU WB 1C WH | 10.1 W |
| 911401550046 | GD700B P42 2XLED21 930PW PSU MB WH | 42.4 W | 911401547046 | ST700T P10 LED12 830 PSU WB 1C BK | 10.1 W |
| 911401548346 | RS700B P21 LED22 940PW PSU MB WH | 21.2 W | 911401547146 | ST700T P10 LED12 830 PSU MB 1C WH | 10.1 W |
| 911401548446 | RS700B P21 LED20 930PW PSU WB WH | 21.2 W | 911401547246 | ST700T P10 LED12 830 PSU MB 1C BK | 10.1 W |
| 911401548746 | RS700B P21 LED21 930PW PSU MB WH | 21.2 W | 911401550346 | GD700B P16 2XLED10 830 PSU MB WH | 16.5 W |
| 911401548846 | RS700B P21 LED20 930PC PSU MB WH | 21.2 W | 911401550446 | GD700B P16 2XLED10 830 PSU MB BK | 16.5 W |
| 911401548946 | RS700B P8 LED10 830 PSU WB WH | 8.2 W | | | |

Mechanical and Housing

| Order Code | Full Product Name | Housing Color |
|--------------|-------------------------------------|---------------|
| 911401548646 | RS700B P21 LED21 930PW PSU NB BK | Black |
| 911401547446 | RS700B P40 LED44 930PW PSU WB WH | White |
| 911401547646 | RS700B P40 LED46 930PW PSU MB BK | Black |
| 911401546246 | ST700T P21 LED22 830 PSU WB 1C WH | White |
| 911401549046 | GD700B P30 LED33 930PC PSU WB WH | White |
| 911401549146 | GD700B P21 LED14 940PW PSU MB WH HB | White |
| 911401549246 | GD700B P21 LED21 930PW PSU MB WH | White |
| 911401549646 | GD700B P8 LED10 830 PSU MB WH | White |
| 911401550246 | GD700B P42 2XLED21 930PW PSU MB BK | Black |
| 911401549546 | GD700B P21 LED21 930PW PSU MB BK | Black |
| 911401549746 | GD700B P8 LED10 830 PSU MB BK | Black |
| 911401547346 | RS700B P40 LED47 940PW PSU MB WH | White |
| 911401547546 | RS700B P40 LED46 930PW PSU MB WH | White |
| 911401547746 | RS700B P40 LED43 930PC PSU MB WH | White |
| 911401547846 | RS700B P30 LED37 940PW PSU MB WH | White |
| 911401547946 | RS700B P30 LED36 930PW PSU WB WH | White |
| 911401548146 | RS700B P30 LED36 930PW PSU MB WH | White |
| 911401548246 | RS700B P30 LED34 930PC PSU MB WH | White |
| 911401550046 | GD700B P42 2XLED21 930PW PSU MB WH | White |
| 911401548346 | RS700B P21 LED22 940PW PSU MB WH | White |
| 911401548446 | RS700B P21 LED20 930PW PSU WB WH | White |
| 911401548746 | RS700B P21 LED21 930PW PSU MB WH | White |
| 911401548846 | RS700B P21 LED20 930PC PSU MB WH | White |
| 911401548946 | RS700B P8 LED10 830 PSU WB WH | White |

| Order Code | Full Product Name | Housing Color |
|--------------|--|---------------|
| 911401550546 | RS700B P8 LED10 830 PSU MB WH | White |
| 911401548046 | RS700B P30 LED36 930PW PSU WB BK | Black |
| 911401542646 | ST700T P41 LED41 930PC PSU WB 1C WH | White |
| 911401542946 | ST700T P41 LED41 930PC PSU WB 1C BK | Black |
| 911401543146 | ST700T P41 LED43 930PC PSU MB 1C WH | White |
| 911401543246 | ST700T P41 LED43 930PC PSU MB 1C BK | Black |
| 911401544346 | ST700T P35 LED37 930PC PSU WB 1C WH | White |
| 911401544746 | ST700T P35 LED37 930PC PSU MB 1C WH | White |
| 911401544946 | ST700T P35 LED37 930PC PSU MB 1C BK | Black |
| 911401545146 | ST700T P21 LED19 930PC PSU WB 1C WH | White |
| 911401545346 | ST700T P21 LED19 930PC PSU WB 1C BK | Black |
| 911401545546 | ST700T P21 LED20 930PC PSU NB 1C WH | White |
| 911401545646 | ST700T P21 LED20 930PC PSU NB 1C BK | Black |
| 911401545946 | ST700T P21 LED20 930PC PSU MB 1C WH | White |
| 911401546046 | ST700T P21 LED13 930PC PSU MB 1C BK HB | Black |
| 911401546146 | ST700T P21 LED20 930PC PSU MB 1C BK | Black |
| 911401546446 | ST700T P21 LED22 830 PSU WB 1C BK | Black |
| 911401546946 | ST700T P10 LED12 830 PSU WB 1C WH | White |
| 911401547046 | ST700T P10 LED12 830 PSU WB 1C BK | Black |
| 911401547146 | ST700T P10 LED12 830 PSU MB 1C WH | White |
| 911401547246 | ST700T P10 LED12 830 PSU MB 1C BK | Black |
| 911401550346 | GD700B P16 2XLED10 830 PSU MB WH | White |
| 911401550446 | GD700B P16 2XLED10 830 PSU MB BK | Black |

Approval and Application

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 911401548646 | RS700B P21 LED21 930PW PSU NB BK | -15 to +35 °C |
| 911401547446 | RS700B P40 LED44 930PW PSU WB WH | -15 to +35 °C |
| 911401547646 | RS700B P40 LED46 930PW PSU MB BK | -15 to +35 °C |
| 911401546246 | ST700T P21 LED22 830 PSU WB 1C WH | -20 °C to 35 °C |
| 911401549046 | GD700B P30 LED33 930PC PSU WB WH | -15 to +35 °C |
| 911401549146 | GD700B P21 LED14 940PW PSU MB WH HB | -15 to +35 °C |
| 911401549246 | GD700B P21 LED21 930PW PSU MB WH | -15 to +35 °C |
| 911401549646 | GD700B P8 LED10 830 PSU MB WH | -15 to +35 °C |
| 911401550246 | GD700B P42 2XLED21 930PW PSU MB BK | -15 to +35 °C |
| 911401549546 | GD700B P21 LED21 930PW PSU MB BK | -15 to +35 °C |
| 911401549746 | GD700B P8 LED10 830 PSU MB BK | -15 to +35 °C |
| 911401547346 | RS700B P40 LED47 940PW PSU MB WH | -15 to +35 °C |
| 911401547546 | RS700B P40 LED46 930PW PSU MB WH | -15 to +35 °C |
| 911401547746 | RS700B P40 LED43 930PC PSU MB WH | -15 to +35 °C |
| 911401547846 | RS700B P30 LED37 940PW PSU MB WH | -15 to +35 °C |
| 911401547946 | RS700B P30 LED36 930PW PSU WB WH | -15 to +35 °C |
| 911401548146 | RS700B P30 LED36 930PW PSU MB WH | -15 to +35 °C |
| 911401548246 | RS700B P30 LED34 930PC PSU MB WH | -15 to +35 °C |
| 911401550046 | GD700B P42 2XLED21 930PW PSU MB WH | -15 to +35 °C |
| 911401548346 | RS700B P21 LED22 940PW PSU MB WH | -15 to +35 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|---|---------------------------|
| 911401548446 | RS700B P21 LED20 930PW PSU WB WH | -15 to +35 °C |
| 911401548746 | RS700B P21 LED21 930PW PSU MB WH | -15 to +35 °C |
| 911401548846 | RS700B P21 LED20 930PC PSU MB WH | -15 to +35 °C |
| 911401548946 | RS700B P8 LED10 830 PSU WB WH | -15 to +35 °C |
| 911401550546 | RS700B P8 LED10 830 PSU MB WH | -15 to +35 °C |
| 911401548046 | RS700B P30 LED36 930PW PSU WB BK | -15 to +35 °C |
| 911401542646 | ST700T P41 LED41 930PC PSU WB 1C WH | -20 °C to 35 °C |
| 911401542946 | ST700T P41 LED41 930PC PSU WB 1C BK | -20 °C to 35 °C |
| 911401543146 | ST700T P41 LED43 930PC PSU MB 1C WH | -20 °C to 35 °C |
| 911401543246 | ST700T P41 LED43 930PC PSU MB 1C BK | -20 °C to 35 °C |
| 911401544346 | ST700T P35 LED37 930PC PSU WB 1C WH | -20 °C to 35 °C |
| 911401544746 | ST700T P35 LED37 930PC PSU MB 1C WH | -20 °C to 35 °C |
| 911401544946 | ST700T P35 LED37 930PC PSU MB 1C BK | -20 °C to 35 °C |
| 911401545146 | ST700T P21 LED19 930PC PSU WB 1C WH | -20 °C to 35 °C |
| 911401545346 | ST700T P21 LED19 930PC PSU WB 1C BK | -20 °C to 35 °C |
| 911401545546 | ST700T P21 LED20 930PC PSU NB 1C WH | -20 °C to 35 °C |
| 911401545646 | ST700T P21 LED20 930PC PSU NB 1C BK | -20 °C to 35 °C |
| 911401545946 | ST700T P21 LED20 930PC PSU MB 1C WH | -20 °C to 35 °C |
| 911401546046 | ST700T P21 LED13 930PC PSU MB 1C BK HB | -20 °C to 35 °C |
| 911401546146 | ST700T P21 LED20 930PC PSU MB 1C BK | -20 °C to 35 °C |
| 911401546446 | ST700T P21 LED22 830 PSU WB 1C BK | -20 °C to 35 °C |

TrueFashion EM

| Order Code | Full Product Name | Ambient temperature range |
|--------------|-----------------------------------|---------------------------|
| 911401546946 | ST700T P10 LED12 830 PSU WB 1C WH | -20 °C to 35 °C |
| 911401547046 | ST700T P10 LED12 830 PSU WB 1C BK | -20 °C to 35 °C |
| 911401547146 | ST700T P10 LED12 830 PSU MB 1C WH | -20 °C to 35 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|-----------------------------------|---------------------------|
| 911401547246 | ST700T P10 LED12 830 PSU MB 1C BK | -20 °C to 35 °C |
| 911401550346 | GD700B P16 2XLED10 830 PSU MB WH | -15 to +35 °C |
| 911401550446 | GD700B P16 2XLED10 830 PSU MB BK | -15 to +35 °C |

