



Small in size, big in quality

TrueFashion EM

TrueFashion is the LED projector family answering miniaturization and presentation needs of specialized retailers. Firstly, these miniaturized spots with clean and fine detailing offer contemporary design and blend seamlessly into your store interior for a tailor-made look. Secondly, it provides high quality accentuation effect thanks to its innovative OptiAccent lens technology (FPO), which provides higher central intensity beam without spill light to maximize the contrast ratio hence optimize the accent effect. Especially in challenging narrow spot (12D) and spot (18D) applications, the difference of OptiAccent to Chip on Board and reflector optics is like day and night. OptiAccent also reduces direct glare by a factor of 5 to enable superior visual comfort. Lastly, TrueFashion also has the light spectra taken care of: the specially designed Philips LED flavors enhance colors (saturation) and whites, while offering high degree of fidelity (exceeds CRI90). This is how TrueFashion ensures a superior light experience in your retail applications.

Benefits

- High-impact and dramatic accentuation effect
- Unobtrusive and flexible lighting installation
- Bright whites, crisp blacks, vibrant colors
- Increased visual comfort

Features

- Miniaturized spot head in the diameter of 66mm for the Mini and 80mm for the Compact size
- OptiAccent (FPO) Lens technology for maximizing central intensity (up to 40%), eliminating spill light/halo in compared to a traditional Chip-On Board LED and reflector optical system, hence offering high contrast accentuation as opposed to a flat and vague light effect (in Compact only)
- Philips LED flavors: Premium White and Premium Color, CRI exceeds 90 and 3000K (ask your sales contact for different requests)
- Smooth powder coated White or Black paint finish (ask your sales contact for different requests)
- Extra narrow beam spot of 6° with 64K Candela central beam
- Full range of beam spread: 6° / 12° /18° /24° /30° /36° (6° in TrueFashion Highlight, and 12°,24°,36° in Compact only)

Application

- Fashion
- Retail
- Hospitality
- Food and Large Retailers

Warnings and Safety

- The luminaire should be mounted outside of arm's reach
- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements

Versions



RS700B LED10 LED20 BK



RTP-OF-RS700B-TrueFashion-EM



RS700B LED30 LED40 BK



RTP-OF-ST700T-TrueFashion-EM



GD700B 1 head WH



RTP-OF-GD700B-TrueFashion-EM



RS700B LED10 LED20 WH












GD700B 2 heads WH

Versions










GD700B 2 heads BK

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	Lens
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401548646	RS700B P21 LED21 930PW PSU NB BK	3000 K	90	101 lm/W	2,147 lm
911401547446	RS700B P40 LED44 930PW PSU WB WH	3000 K	90	109 lm/W	4,421 lm
911401547646	RS700B P40 LED46 930PW PSU MB BK	3000 K	90	114 lm/W	4,596 lm
911401546246	ST700T P21 LED22 830 PSU WB 1C WH	2700 K	80	104 lm/W	2,177 lm
911401549046	GD700B P30 LED33 930PC PSU WB WH	3000 K	90	109 lm/W	3,347 lm
911401549446	GD700B P21 LED21 930PW PSU MB WH	3000 K	90	101 lm/W	2,147 lm
911401549146	GD700B P21 LED14 940PW PSU MB WH HB	4000 K	90	68 lm/W	1,432 lm
911401549246	GD700B P21 LED21 930PW PSU MB WH	3000 K	90	101 lm/W	2,147 lm
911401549646	GD700B P8 LED10 830 PSU MB WH	3000 K	80	126 lm/W	1,030 lm
911401543446	ST700T P35 LED38 930PW PSU WB 3C BK	3000 K	90	111 lm/W	3,865 lm
911401543546	ST700T P35 LED40 930PW PSU MB 3C WH	3000 K	90	115 lm/W	4,018 lm
911401543646	ST700T P35 LED40 930PW PSU MB 3C BK	3000 K	90	115 lm/W	4,018 lm
911401543846	ST700T P35 LED38 930PW PSD VLC WB WH	3000 K	90	111 lm/W	3,865 lm
911401544046	ST700T P35 LED38 930PW PSD VLC WB BK	3000 K	90	111 lm/W	3,865 lm
911401549546	GD700B P21 LED21 930PW PSU MB BK	3000 K	90	101 lm/W	2,147 lm
911401549746	GD700B P8 LED10 830 PSU MB BK	3000 K	80	126 lm/W	1,030 lm
911401547346	RS700B P40 LED47 940PW PSU MB WH	4000 K	90	118 lm/W	4,736 lm
911401547546	RS700B P40 LED46 930PW PSU MB WH	3000 K	90	114 lm/W	4,596 lm
911401547746	RS700B P40 LED43 930PC PSU MB WH	3000 K	90	106 lm/W	4,282 lm
911401547846	RS700B P30 LED37 940PW PSU MB WH	4000 K	90	122 lm/W	3,756 lm
911401547946	RS700B P30 LED36 930PW PSU WB WH	3000 K	90	117 lm/W	3,600 lm
911401548146	RS700B P30 LED36 930PW PSU MB WH	3000 K	90	118 lm/W	3,645 lm
911401548246	RS700B P30 LED34 930PC PSU MB WH	3000 K	90	110 lm/W	3,389 lm
911401550146	GD700B P42 2XLED21 930PW PSU MB WH	3000 K	90	101 lm/W	4,295 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401548346	RS700B P21 LED22 940PW PSU MB WH	4000 K	90	104 lm/W	2,213 lm
911401548446	RS700B P21 LED20 930PW PSU WB WH	3000 K	90	96 lm/W	2,021 lm
911401548746	RS700B P21 LED21 930PW PSU MB WH	3000 K	90	101 lm/W	2,147 lm
911401548846	RS700B P21 LED20 930PC PSU MB WH	3000 K	90	94 lm/W	1,997 lm
911401548946	RS700B P8 LED10 830 PSU WB WH	3000 K	80	118 lm/W	969 lm
911401550546	RS700B P8 LED10 830 PSU MB WH	3000 K	80	125 lm/W	1,029 lm
911401542646	ST700T P41 LED41 930PC PSU WB 1C WH	3000 K	90	100 lm/W	4,120 lm
911401542946	ST700T P41 LED41 930PC PSU WB 1C BK	3000 K	90	100 lm/W	4,120 lm
911401543146	ST700T P41 LED43 930PC PSU MB 1C WH	3000 K	90	104 lm/W	4,282 lm
911401543246	ST700T P41 LED43 930PC PSU MB 1C BK	3000 K	90	104 lm/W	4,282 lm
911401544346	ST700T P35 LED37 930PC PSU WB 1C WH	3000 K	90	105 lm/W	3,699 lm
911401544746	ST700T P35 LED37 930PC PSU MB 1C WH	3000 K	90	106 lm/W	3,746 lm
911401544946	ST700T P35 LED37 930PC PSU MB 1C BK	3000 K	90	106 lm/W	3,746 lm
911401545146	ST700T P21 LED19 930PC PSU WB 1C WH	3000 K	90	91 lm/W	1,913 lm
911401545346	ST700T P21 LED19 930PC PSU WB 1C BK	3000 K	90	91 lm/W	1,913 lm
911401545546	ST700T P21 LED20 930PC PSU NB 1C WH	3000 K	90	96 lm/W	2,032 lm
911401545646	ST700T P21 LED20 930PC PSU NB 1C BK	3000 K	90	96 lm/W	2,032 lm
911401545946	ST700T P21 LED20 930PC PSU MB 1C WH	3000 K	90	96 lm/W	2,032 lm
911401546046	ST700T P21 LED13 930PC PSU MB 1C BK HB	3000 K	90	62 lm/W	1,315 lm
911401546146	ST700T P21 LED20 930PC PSU MB 1C BK	3000 K	90	96 lm/W	2,032 lm
911401546346	ST700T P21 LED22 830 PSU WB 1C WH	3000 K	80	104 lm/W	2,177 lm
911401546446	ST700T P21 LED22 830 PSU WB 1C BK	4000 K	80	104 lm/W	2,177 lm
911401546946	ST700T P10 LED12 830 PSU WB 1C WH	3000 K	80	118 lm/W	1,186 lm
911401547046	ST700T P10 LED12 830 PSU WB 1C BK	4000 K	80	118 lm/W	1,186 lm
911401547146	ST700T P10 LED12 830 PSU MB 1C WH	2700 K	80	125 lm/W	1,260 lm

Order Code	Full Product Name	Correlated Color	Color	Luminous	Luminous Flux
		Temperature	rendering	Efficacy (rated)	
		(Nom)	index (CRI)	(Nom)	
911401547246	ST700T P10 LED12 830 PSU MB 1C BK	3000 K	80	125 lm/W	1,260 lm
911401549946	GD700B P42 2XLED21 930PW PSU MB WH	3000 K	90	101 lm/W	4,295 lm
911401550346	GD700B P16 2XLED10 830 PSU MB WH	3000 K	80	125 lm/W	2,059 lm
911401550446	GD700B P16 2XLED10 830 PSU MB BK	3000 K	80	125 lm/W	2,059 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401548646	RS700B P21 LED21 930PW PSU NB BK	21.2 W	911401548846	RS700B P21 LED20 930PC PSU MB WH	21.2 W
911401547446	RS700B P40 LED44 930PW PSU WB WH	40.3 W	911401548946	RS700B P8 LED10 830 PSU WB WH	8.2 W
911401547646	RS700B P40 LED46 930PW PSU MB BK	40.3 W	911401550546	RS700B P8 LED10 830 PSU MB WH	8.2 W
911401546246	ST700T P21 LED22 830 PSU WB 1C WH	21 W	911401542646	ST700T P41 LED41 930PC PSU WB 1C WH	41.2 W
911401549046	GD700B P30 LED33 930PC PSU WB WH	30.8 W	911401542946	ST700T P41 LED41 930PC PSU WB 1C BK	41.2 W
911401549446	GD700B P21 LED21 930PW PSU MB WH	21.2 W	911401543146	ST700T P41 LED43 930PC PSU MB 1C WH	41.2 W
911401549146	GD700B P21 LED14 940PW PSU MB WH HB	21.2 W	911401543246	ST700T P41 LED43 930PC PSU MB 1C BK	41.2 W
911401549246	GD700B P21 LED21 930PW PSU MB WH	21.2 W	911401544346	ST700T P35 LED37 930PC PSU WB 1C WH	35.4 W
911401549646	GD700B P8 LED10 830 PSU MB WH	8.2 W	911401544746	ST700T P35 LED37 930PC PSU MB 1C WH	35.4 W
911401543446	ST700T P35 LED38 930PW PSU WB 3C BK	35 W	911401544946	ST700T P35 LED37 930PC PSU MB 1C BK	35.4 W
911401543546	ST700T P35 LED40 930PW PSU MB 3C WH	35 W	911401545146	ST700T P21 LED19 930PC PSU WB 1C WH	21 W
911401543646	ST700T P35 LED40 930PW PSU MB 3C BK	35 W	911401545346	ST700T P21 LED19 930PC PSU WB 1C BK	21 W
911401543846	ST700T P35 LED38 930PW PSD VLC WB WH	35 W	911401545546	ST700T P21 LED20 930PC PSU NB 1C WH	21 W
911401544046	ST700T P35 LED38 930PW PSD VLC WB BK	35 W	911401545646	ST700T P21 LED20 930PC PSU NB 1C BK	21 W
911401549546	GD700B P21 LED21 930PW PSU MB BK	21.2 W	911401545946	ST700T P21 LED20 930PC PSU MB 1C WH	21 W
911401549746	GD700B P8 LED10 830 PSU MB BK	8.2 W	911401546046	ST700T P21 LED13 930PC PSU MB 1C BK HB	21 W
911401547346	RS700B P40 LED47 940PW PSU MB WH	40.3 W	911401546146	ST700T P21 LED20 930PC PSU MB 1C BK	21 W
911401547546	RS700B P40 LED46 930PW PSU MB WH	40.3 W	911401546346	ST700T P21 LED22 830 PSU WB 1C WH	21 W
911401547746	RS700B P40 LED43 930PC PSU MB WH	40.3 W	911401546446	ST700T P21 LED22 830 PSU WB 1C BK	21 W
911401547846	RS700B P30 LED37 940PW PSU MB WH	30.8 W	911401546946	ST700T P10 LED12 830 PSU WB 1C WH	10.1 W
911401547946	RS700B P30 LED36 930PW PSU WB WH	30.8 W	911401547046	ST700T P10 LED12 830 PSU WB 1C BK	10.1 W
911401548146	RS700B P30 LED36 930PW PSU MB WH	30.8 W	911401547146	ST700T P10 LED12 830 PSU MB 1C WH	10.1 W
911401548246	RS700B P30 LED34 930PC PSU MB WH	30.8 W	911401547246	ST700T P10 LED12 830 PSU MB 1C BK	10.1 W
911401550146	GD700B P42 2XLED21 930PW PSU MB WH	42.4 W	911401549946	GD700B P42 2XLED21 930PW PSU MB WH	42.4 W
911401548346	RS700B P21 LED22 940PW PSU MB WH	21.2 W	911401550346	GD700B P16 2XLED10 830 PSU MB WH	16.5 W
911401548446	RS700B P21 LED20 930PW PSU WB WH	21.2 W	911401550446	GD700B P16 2XLED10 830 PSU MB BK	16.5 W
911401548746	RS700B P21 LED21 930PW PSU MB WH	21.2 W			

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401548646	RS700B P21 LED21 930PW PSU NB BK	-	911401549146	GD700B P21 LED14 940PW PSU MB WH HB	-
911401547446	RS700B P40 LED44 930PW PSU WB WH	-	911401549246	GD700B P21 LED21 930PW PSU MB WH	-
911401547646	RS700B P40 LED46 930PW PSU MB BK	-	911401549646	GD700B P8 LED10 830 PSU MB WH	-
911401546246	ST700T P21 LED22 830 PSU WB 1C WH	-	911401543446	ST700T P35 LED38 930PW PSU WB 3C BK	-
911401549046	GD700B P30 LED33 930PC PSU WB WH	-	911401543546	ST700T P35 LED40 930PW PSU MB 3C WH	-
911401549446	GD700B P21 LED21 930PW PSU MB WH	-	911401543646	ST700T P35 LED40 930PW PSU MB 3C BK	-

Order Code	Full Product Name	Dimmable
911401543846	ST700T P35 LED38 930PW PSD VLC WB WH	DALI
911401544046	ST700T P35 LED38 930PW PSD VLC WB BK	DALI
911401549546	GD700B P21 LED21 930PW PSU MB BK	-
911401549746	GD700B P8 LED10 830 PSU MB BK	-
911401547346	RS700B P40 LED47 940PW PSU MB WH	-
911401547546	RS700B P40 LED46 930PW PSU MB WH	-
911401547746	RS700B P40 LED37 930PC PSU MB WH	-
911401547846	RS700B P30 LED37 940PW PSU MB WH	-
911401547946	RS700B P30 LED36 930PW PSU WB WH	-
911401548146	RS700B P30 LED36 930PW PSU MB WH	-
911401548246	RS700B P30 LED34 930PC PSU MB WH	-
911401550146	GD700B P42 2XLED21 930PW PSU MB WH	-
911401548346	RS700B P21 LED22 940PW PSU MB WH	-
911401548446	RS700B P21 LED20 930PW PSU WB WH	-
911401548746	RS700B P21 LED21 930PW PSU MB WH	-
911401548846	RS700B P21 LED20 930PC PSU MB WH	-
911401548946	RS700B P8 LED10 830 PSU WB WH	-
911401550546	RS700B P8 LED10 830 PSU MB WH	-
911401542646	ST700T P41 LED41 930PC PSU WB 1C WH	-
911401542946	ST700T P41 LED41 930PC PSU WB 1C BK	-
911401543146	ST700T P41 LED43 930PC PSU MB 1C WH	-

Order Code	Full Product Name	Dimmable
911401543246	ST700T P41 LED43 930PC PSU MB 1C BK	-
911401544346	ST700T P35 LED37 930PC PSU WB 1C WH	-
911401544746	ST700T P35 LED37 930PC PSU MB 1C WH	-
911401544946	ST700T P35 LED37 930PC PSU MB 1C BK	-
911401545146	ST700T P21 LED19 930PC PSU WB 1C WH	-
911401545346	ST700T P21 LED19 930PC PSU WB 1C BK	-
911401545546	ST700T P21 LED20 930PC PSU NB 1C WH	-
911401545646	ST700T P21 LED20 930PC PSU NB 1C BK	-
911401545946	ST700T P21 LED20 930PC PSU MB 1C WH	-
911401546046	ST700T P21 LED13 930PC PSU MB 1C BK HB	-
911401546146	ST700T P21 LED20 930PC PSU MB 1C BK	-
911401546346	ST700T P21 LED22 830 PSU WB 1C WH	-
911401546446	ST700T P21 LED22 830 PSU WB 1C BK	-
911401546946	ST700T P10 LED12 830 PSU WB 1C WH	-
911401547046	ST700T P10 LED12 830 PSU WB 1C BK	-
911401547146	ST700T P10 LED12 830 PSU MB 1C WH	-
911401547246	ST700T P10 LED12 830 PSU MB 1C BK	-
911401549946	GD700B P42 2XLED21 930PW PSU MB WH	-
911401550346	GD700B P16 2XLED10 830 PSU MB WH	-
911401550446	GD700B P16 2XLED10 830 PSU MB BK	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401548646	RS700B P21 LED21 930PW PSU NB BK	Black
911401547446	RS700B P40 LED44 930PW PSU WB WH	White
911401547646	RS700B P40 LED46 930PW PSU MB BK	Black
911401546246	ST700T P21 LED22 830 PSU WB 1C WH	White
911401549046	GD700B P30 LED33 930PC PSU WB WH	White
911401549446	GD700B P21 LED21 930PW PSU MB WH	White
911401549146	GD700B P21 LED14 940PW PSU MB WH HB	White
911401549246	GD700B P21 LED21 930PW PSU MB WH	White
911401549646	GD700B P8 LED10 830 PSU MB WH	White
911401543446	ST700T P35 LED38 930PW PSU WB 3C BK	Black
911401543546	ST700T P35 LED40 930PW PSU MB 3C WH	White
911401543646	ST700T P35 LED40 930PW PSU MB 3C BK	Black
911401543846	ST700T P35 LED38 930PW PSD VLC WB WH	White
911401544046	ST700T P35 LED38 930PW PSD VLC WB BK	Black
911401549546	GD700B P21 LED21 930PW PSU MB BK	Black
911401549746	GD700B P8 LED10 830 PSU MB BK	Black
911401547346	RS700B P40 LED47 940PW PSU MB WH	White
911401547546	RS700B P40 LED46 930PW PSU MB WH	White
911401547746	RS700B P40 LED43 930PC PSU MB WH	White
911401547846	RS700B P30 LED37 940PW PSU MB WH	White
911401547946	RS700B P30 LED36 930PW PSU WB WH	White
911401548146	RS700B P30 LED36 930PW PSU MB WH	White
911401548246	RS700B P30 LED34 930PC PSU MB WH	White
911401550146	GD700B P42 2XLED21 930PW PSU MB WH	White
911401548346	RS700B P21 LED22 940PW PSU MB WH	White
911401548446	RS700B P21 LED20 930PW PSU WB WH	White
911401548746	RS700B P21 LED21 930PW PSU MB WH	White

Order Code	Full Product Name	Housing Color
911401548846	RS700B P21 LED20 930PC PSU MB WH	White
911401548946	RS700B P8 LED10 830 PSU WB WH	White
911401550546	RS700B P8 LED10 830 PSU MB WH	White
911401542646	ST700T P41 LED41 930PC PSU WB 1C WH	White
911401542946	ST700T P41 LED41 930PC PSU WB 1C BK	Black
911401543146	ST700T P41 LED43 930PC PSU MB 1C WH	White
911401543246	ST700T P41 LED43 930PC PSU MB 1C BK	Black
911401544346	ST700T P35 LED37 930PC PSU WB 1C WH	White
911401544746	ST700T P35 LED37 930PC PSU MB 1C WH	White
911401544946	ST700T P35 LED37 930PC PSU MB 1C BK	Black
911401545146	ST700T P21 LED19 930PC PSU WB 1C WH	White
911401545346	ST700T P21 LED19 930PC PSU WB 1C BK	Black
911401545546	ST700T P21 LED20 930PC PSU NB 1C WH	White
911401545646	ST700T P21 LED20 930PC PSU NB 1C BK	Black
911401545946	ST700T P21 LED20 930PC PSU MB 1C WH	White
911401546046	ST700T P21 LED13 930PC PSU MB 1C BK HB	Black
911401546146	ST700T P21 LED20 930PC PSU MB 1C BK	Black
911401546346	ST700T P21 LED22 830 PSU WB 1C WH	White
911401546446	ST700T P21 LED22 830 PSU WB 1C BK	Black
911401546946	ST700T P10 LED12 830 PSU WB 1C WH	White
911401547046	ST700T P10 LED12 830 PSU WB 1C BK	Black
911401547146	ST700T P10 LED12 830 PSU MB 1C WH	White
911401547246	ST700T P10 LED12 830 PSU MB 1C BK	Black
911401549946	GD700B P42 2XLED21 930PW PSU MB WH	White
911401550346	GD700B P16 2XLED10 830 PSU MB WH	White
911401550446	GD700B P16 2XLED10 830 PSU MB BK	Black

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Order Code	Full Product Name	Ambient temperature range
911401548646	RS700B P21 LED21 930PW PSU NB BK	-15 to +35 °C	911401548446	RS700B P21 LED20 930PW PSU WB WH	-15 to +35 °C
911401547446	RS700B P40 LED44 930PW PSU WB WH	-15 to +35 °C	911401548746	RS700B P21 LED21 930PW PSU MB WH	-15 to +35 °C
911401547646	RS700B P40 LED46 930PW PSU MB BK	-15 to +35 °C	911401548846	RS700B P21 LED20 930PC PSU MB WH	-15 to +35 °C
911401546246	ST700T P21 LED22 830 PSU WB 1C WH	-20 °C to 35 °C	911401548946	RS700B P8 LED10 830 PSU WB WH	-15 to +35 °C
911401549046	GD700B P30 LED33 930PC PSU WB WH	-15 to +35 °C	911401550546	RS700B P8 LED10 830 PSU MB WH	-15 to +35 °C
911401549446	GD700B P21 LED21 930PW PSU MB WH	-15 to +35 °C	911401542646	ST700T P41 LED41 930PC PSU WB 1C WH	-20 °C to 35 °C
911401549146	GD700B P21 LED14 940PW PSU MB WH	-15 to +35 °C	911401542946	ST700T P41 LED41 930PC PSU WB 1C BK	-20 °C to 35 °C
	HB		911401543146	ST700T P41 LED43 930PC PSU MB 1C WH	-20 °C to 35 °C
911401549246	GD700B P21 LED21 930PW PSU MB WH	-15 to +35 °C	911401543246	ST700T P41 LED43 930PC PSU MB 1C BK	-20 °C to 35 °C
911401549646	GD700B P8 LED10 830 PSU MB WH	-15 to +35 °C	911401544346	ST700T P35 LED37 930PC PSU WB 1C WH	-20 °C to 35 °C
911401543446	ST700T P35 LED38 930PW PSU WB 3C BK	-20 °C to 35 °C	911401544746	ST700T P35 LED37 930PC PSU MB 1C WH	-20 °C to 35 °C
911401543546	ST700T P35 LED40 930PW PSU MB 3C	-20 °C to 35 °C	911401544946	ST700T P35 LED37 930PC PSU MB 1C BK	-20 °C to 35 °C
	WH		911401545146	ST700T P21 LED19 930PC PSU WB 1C WH	-20 °C to 35 °C
911401543646	ST700T P35 LED40 930PW PSU MB 3C BK	-20 °C to 35 °C	911401545346	ST700T P21 LED19 930PC PSU WB 1C BK	-20 °C to 35 °C
911401543846	ST700T P35 LED38 930PW PSD VLC WB	-20 °C to 35 °C	911401545546	ST700T P21 LED20 930PC PSU NB 1C WH	-20 °C to 35 °C
	WH		911401545646	ST700T P21 LED20 930PC PSU NB 1C BK	-20 °C to 35 °C
911401544046	ST700T P35 LED38 930PW PSD VLC WB	-20 °C to 35 °C	911401545946	ST700T P21 LED20 930PC PSU MB 1C WH	-20 °C to 35 °C
	BK		911401546046	ST700T P21 LED13 930PC PSU MB 1C BK	-20 °C to 35 °C
911401549546	GD700B P21 LED21 930PW PSU MB BK	-15 to +35 °C		HB	
911401549746	GD700B P8 LED10 830 PSU MB BK	-15 to +35 °C	911401546146	ST700T P21 LED20 930PC PSU MB 1C BK	-20 °C to 35 °C
911401547346	RS700B P40 LED47 940PW PSU MB WH	-15 to +35 °C	911401546346	ST700T P21 LED22 830 PSU WB 1C WH	-20 °C to 35 °C
911401547546	RS700B P40 LED46 930PW PSU MB WH	-15 to +35 °C	911401546446	ST700T P21 LED22 830 PSU WB 1C BK	-20 °C to 35 °C
911401547746	RS700B P40 LED43 930PC PSU MB WH	-15 to +35 °C	911401546946	ST700T P10 LED12 830 PSU WB 1C WH	-20 °C to 35 °C
911401547846	RS700B P30 LED37 940PW PSU MB WH	-15 to +35 °C	911401547046	ST700T P10 LED12 830 PSU WB 1C BK	-20 °C to 35 °C
911401547946	RS700B P30 LED36 930PW PSU WB WH	-15 to +35 °C	911401547146	ST700T P10 LED12 830 PSU MB 1C WH	-20 °C to 35 °C
911401548146	RS700B P30 LED36 930PW PSU MB WH	-15 to +35 °C	911401547246	ST700T P10 LED12 830 PSU MB 1C BK	-20 °C to 35 °C
911401548246	RS700B P30 LED34 930PC PSU MB WH	-15 to +35 °C	911401549946	GD700B P42 2XLED21 930PW PSU MB	-15 to +35 °C
911401550146	GD700B P42 2XLED21 930PW PSU MB	-15 to +35 °C		WH	
	WH		911401550346	GD700B P16 2XLED10 830 PSU MB WH	-15 to +35 °C
911401548346	RS700B P21 LED22 940PW PSU MB WH	-15 to +35 °C	911401550446	GD700B P16 2XLED10 830 PSU MB BK	-15 to +35 °C

