



Affordable, plastic, A-shape lamps that meet industry standards and offer quality and best-in-class dimming ideal for commercial spaces

CorePro Plastic (Dimmable) A-Shape Lamps

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Benefits

- Best-in-class dimmability
- Long lifetime that reduces the need for replacements
- Title 20 listed – can be sold in California

Features

- Plastic bulb
- Dimmable
- Long lifetime up to 25,000 hours
- Very good light quality with excellent color rendering (CRI90)

CorePro Plastic (Dimmable) A-Shape Lamps

Application

- Light Commercial
- Retail

Versions



LEDbulb CorePro 19.5-150W E27
A67 Frosted 827 15D ND




LEDbulb E26 A9 FR 1



LEDbulb A21 GU24





Dimensional drawing



Product	D	C
16A21/PER/930/P/GU24/DIM 4/1FB T20	77 mm	140 mm

CorePro Plastic (Dimmable) A-Shape Lamps

Dimensional drawing



Product	D	C
12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	60 mm	112 mm
12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	60 mm	112 mm
12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	60 mm	112 mm
12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	60 mm	112 mm

Product	D	C
14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	60 mm	117 mm
14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	60 mm	117 mm
14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	60 mm	117 mm
14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	60 mm	117 mm

Product	D	C
29A21/PER/850/FR/P/E26/D/HO 4/1PF	77 mm	138 mm

Product	D	C
5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm
8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm
8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm
8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm
8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	62.5 mm	111.5 mm

CorePro Plastic (Dimmable) A-Shape Lamps

General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime	Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	E26	15,000	15,000	929003784804	14A19/COR/940/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000
929002032304	8.8A19/COR/940/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000	929003784904	14A19/COR/950/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000
929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	E26	-	25,000	929002285204	12.2A19/COR/950/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000
929002036104	8.8A19/COR/927/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000	929002385204	12.2A19/COR/927/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000
929002036204	8.8A19/COR/930/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000	929002385304	12.2A19/COR/930/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000
929002036304	8.8A19/COR/950/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000	929002385404	12.2A19/COR/940/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000
929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	E26	-	25,000	929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	GU24	15,000	15,000
929003784704	14A19/COR/930/FR/P/E26/DI M/T20 6/1CT	E26	-	25,000					

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	250 degree(s)	5000 K	80	850	2,610 lm
929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	4000 K	90	940	800 lm
929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	2700 K	90	927	450 lm
929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	2700 K	90	927	800 lm
929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	3000 K	90	930	800 lm
929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	5000 K	90	950	800 lm
929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	2700 K	90	927	1,500 lm
929003784704	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	3000 K	90	930	1,500 lm
929003784804	14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	4000 K	90	940	1,500 lm

CorePro Plastic (Dimmable) A-Shape Lamps

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003784904	14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	5000 K	90	950	1,500 lm
929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	5000 K	90	950	1,100 lm
929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	2700 K	90	927	1,100 lm
929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	3000 K	90	930	1,100 lm
929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	200 degree(s)	4000 K	90	940	1,100 lm
929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	250 degree(s)	3000 K	90	930	1,600 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	60 Hz	29 W	150 W
929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	60 Hz	8.8 W	60 W
929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	60 Hz	5 W	40 W
929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	60 Hz	8.8 W	60 W
929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	60 Hz	8.8 W	60 W
929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	60 Hz	8.8 W	60 W
929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	-	14 W	100 W
929003784704	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	-	14 W	100 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage Equivalent
929003784804	14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	-	14 W	100 W
929003784904	14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	-	14 W	100 W
929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	60 Hz	12.2 W	75 W
929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	60 Hz	12.2 W	75 W
929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	60 Hz	12.2 W	75 W
929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	60 Hz	12.2 W	75 W
929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	60 Hz	16 W	100 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	100 °C
929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	75 °C
929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	65 °C
929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	75 °C
929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	75 °C
929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	75 °C
929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	100 °C
929003784704	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	100 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929003784804	14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	100 °C
929003784904	14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	100 °C
929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	90 °C
929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	90 °C
929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	90 °C
929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	90 °C
929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	90 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	A21
929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	A19

Order Code	Full Product Name	Bulb Shape
929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	A19
929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	A19






CorePro Plastic (Dimmable) A-Shape Lamps

Order Code	Full Product Name	Bulb Shape
929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	A19
929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	A19
929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	A19
929003784704	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	A19
929003784804	14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	A19
929003784904	14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	A19

Order Code	Full Product Name	Bulb Shape
929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	A19
929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	A19
929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	A19
929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	A19
929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	A21

Approval and Application

Order Code	Full Product Name	Ambient temperature range
929002343133	29A21/PER/850/FR/P/E26/D/HO 4/IPF	-20 °C to 45 °C
929002032304	8.8A19/COR/940/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002035704	5A19/COR/927/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002036104	8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002036204	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002036304	8.8A19/COR/950/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929003784604	14A19/COR/927/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929003784704	14A19/COR/930/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929003784804	14A19/COR/940/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929003784904	14A19/COR/950/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002285204	12.2A19/COR/950/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002385204	12.2A19/COR/927/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002385304	12.2A19/COR/930/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002385404	12.2A19/COR/940/FR/P/E26/DIM/T20 6/1CT	-20 to +45 °C
929002327634	16A21/PER/930/P/GU24/DIM 4/1FB T20	-20 °C to 45 °C



CorePro Plastic (Dimmable) A-Shape Lamps

