



# Built-in technology for additional features

## Specialty Lamps

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Benefits

- Party bulbs, the perfect festive touch for holidays and special occasions
- Dusk to dawn bulbs, is equipped with a built-in light sensor for added security
- 3-way bulbs, offers switching between 3 wattage settings to get exactly the right amount of light when you need it

### Features

- Long lifetime
- Excellent color consistency
- Dusk to Dawn
- Switching between 3 wattage settings

### Application

- Assisted Living
- Residential
- Hospitality

# Specialty Lamps

## Versions




8W (60W) E26 Blue Bulb - RFT



LEDbulb Color A19 E26 Red



LEDbulb A21 E26 FR



LEDbulb Color A19 E26 Orange




LEDbulb Color A19 E26 Blue



LEDbulb A19 E26 FR



8W (60W) E26 Red Bulb - RFT



LEDbulb Color A19 E26 Yellow



8W (60W) E26 Yellow Bulb - RFT



8W (60W) E26 Green Bulb - RFT




LEDbulb Color A19 E26 Green



LEDbulb Color A19 E26 Purple




## Dimensional drawing



Product	D	C
18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	70.6 mm	133.1 mm

# Specialty Lamps

## Dimensional drawing



Product	D	C
8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	61.5 mm	109.8 mm

Product	D	C
8W (60W) E26 Blue Bulb	60 mm	107 mm
8W (60W) E26 Green Bulb	60 mm	107 mm
8W (60W) E26 Red Bulb	60 mm	107 mm
8W (60W) E26 Yellow Bulb	60 mm	107 mm

Product	D	C
4A19/PER/BLUE/G/E26/ND 4/1PF	60 mm	106 mm
4A19/PER/GREEN/G/E26/ND 4/1PF	60 mm	106 mm
4A19/PER/ORANGE/G/E26/ND 4/1PF	60 mm	106 mm
4A19/PER/PURPLE/G/E26/ND 4/1PF	60 mm	106 mm
4A19/PER/RED/G/E26/ND 4/1PF	60 mm	106 mm
4A19/PER/YELLOW/G/E26/ND 4/1PF	60 mm	106 mm

### Light Technical

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

### Operating and Electrical

Input Frequency	60 Hz
Starting Time (Nom)	0.5 s

### Controls and Dimming

Dimmable	No
----------	----

## General Information

## Specialty Lamps

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929001998005	8W (60W) E26 Blue Bulb	E26	10,950 hour(s)	20,000	10,950 hour(s)
929001937053	4A19/PER/RED/G/E26/ND 4/1PF	E26	15,000 hour(s)	20,000	15,000 hour(s)
929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	E26d	15,000 hour(s)	50,000	15,000 hour(s)
929001937153	4A19/PER/ORANGE/G/E26/ND 4/1PF	E26	15,000 hour(s)	20,000	15,000 hour(s)
929001937353	4A19/PER/BLUE/G/E26/ND 4/1PF	E26	15,000 hour(s)	20,000	15,000 hour(s)
929002333693	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	E26	15,000 hour(s)	50,000	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929001997805	8W (60W) E26 Red Bulb	E26	10,950 hour(s)	20,000	10,950 hour(s)
929001937253	4A19/PER/YELLOW/G/E26/ND 4/1PF	E26	15,000 hour(s)	20,000	15,000 hour(s)
929001998105	8W (60W) E26 Yellow Bulb	E26	10,950 hour(s)	20,000	10,950 hour(s)
929001997905	8W (60W) E26 Green Bulb	E26	10,950 hour(s)	20,000	10,950 hour(s)
929001937453	4A19/PER/GREEN/G/E26/ND 4/1PF	E26	15,000 hour(s)	20,000	15,000 hour(s)
929001937553	4A19/PER/PURPLE/G/E26/ND 4/1PF	E26	15,000 hour(s)	20,000	15,000 hour(s)

### Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929001998005	8W (60W) E26 Blue Bulb	120 degree(s)	-	-	-	-
929001937053	4A19/PER/RED/G/E26/ND 4/1PF	330 degree(s)	-	-	Red	-
929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	250 degree(s)	2700 K	90	927	2,150 lm
929001937153	4A19/PER/ORANGE/G/E26/ND 4/1PF	330 degree(s)	-	-	Orange	-
929001937353	4A19/PER/BLUE/G/E26/ND 4/1PF	330 degree(s)	-	-	Blue	-
929002333693	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	220 degree(s)	2700 K	90	927	800 lm
929001997805	8W (60W) E26 Red Bulb	120 degree(s)	-	-	-	-
929001937253	4A19/PER/YELLOW/G/E26/ND 4/1PF	330 degree(s)	-	-	Yellow	-
929001998105	8W (60W) E26 Yellow Bulb	160 degree(s)	-	-	-	-
929001997905	8W (60W) E26 Green Bulb	160 degree(s)	-	-	-	-
929001937453	4A19/PER/GREEN/G/E26/ND 4/1PF	330 degree(s)	-	-	Green	-
929001937553	4A19/PER/PURPLE/G/E26/ND 4/1PF	330 degree(s)	-	-	Purple	-

### Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	Wattage Equivalent
929001998005	8W (60W) E26 Blue Bulb	60 Hz	8 W	40 W
929001937053	4A19/PER/RED/G/E26/ND 4/1PF	60 Hz	4 W	40 W
929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	-	18.5 W	150 W
929001937153	4A19/PER/ORANGE/G/E26/ND 4/1PF	60 Hz	4 W	40 W

Order Code	Full Product Name	Line Frequency	Power	
			Consumption	Wattage Equivalent
929001937353	4A19/PER/BLUE/G/E26/ND 4/1PF	60 Hz	4 W	40 W
929002333693	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	60 Hz	8.8 W	60 W
929001997805	8W (60W) E26 Red Bulb	60 Hz	8 W	40 W
929001937253	4A19/PER/YELLOW/G/E26/ND 4/1PF	60 Hz	4 W	40 W

## Specialty Lamps

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929001998105	8W (60W) E26 Yellow Bulb	60 Hz	8 W	40 W
929001997905	8W (60W) E26 Green Bulb	60 Hz	8 W	40 W
929001937453	4A19/PER/ GREEN/G/E26/ND 4/1PF	60 Hz	4 W	40 W

Order Code	Full Product Name	Line	Power	Wattage
		Frequency	Consumption	Equivalent
929001937553	4A19/PER/ PURPLE/G/E26/ND 4/1PF	60 Hz	4 W	40 W

### Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001998005	8W (60W) E26 Blue Bulb	80 °C
929001937053	4A19/PER/RED/G/E26/ND 4/1PF	125 °C
929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	95 °C
929001937153	4A19/PER/ORANGE/G/E26/ND 4/1PF	125 °C
929001937353	4A19/PER/BLUE/G/E26/ND 4/1PF	125 °C
929002333693	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001997805	8W (60W) E26 Red Bulb	80 °C
929001937253	4A19/PER/YELLOW/G/E26/ND 4/1PF	125 °C
929001998105	8W (60W) E26 Yellow Bulb	80 °C
929001997905	8W (60W) E26 Green Bulb	80 °C
929001937453	4A19/PER/GREEN/G/E26/ND 4/1PF	125 °C
929001937553	4A19/PER/PURPLE/G/E26/ND 4/1PF	125 °C


### Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001998005	8W (60W) E26 Blue Bulb	Frosted	A19
929001937053	4A19/PER/RED/G/E26/ND 4/1PF	Red	A19
929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	Frosted	A21
929001937153	4A19/PER/ORANGE/G/E26/ND 4/1PF	Orange	A19
929001937353	4A19/PER/BLUE/G/E26/ND 4/1PF	Blue	A19
929002333693	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	Frosted	A19

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001997805	8W (60W) E26 Red Bulb	Frosted	A19
929001937253	4A19/PER/YELLOW/G/E26/ND 4/1PF	Yellow	A19
929001998105	8W (60W) E26 Yellow Bulb	Frosted	A19
929001997905	8W (60W) E26 Green Bulb	Frosted	A19
929001937453	4A19/PER/GREEN/G/E26/ND 4/1PF	Green	A19
929001937553	4A19/PER/PURPLE/G/E26/ND 4/1PF	Purple	A19

### Approval and Application

Order Code	Full Product Name	Ambient temperature range
929001998005	8W (60W) E26 Blue Bulb	-20 to +45 °C
929001937053	4A19/PER/RED/G/E26/ND 4/1PF	-20 °C to 45 °C
929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF	-20 to +45 °C
929001937153	4A19/PER/ORANGE/G/E26/ND 4/1PF	-20 °C to 45 °C
929001937353	4A19/PER/BLUE/G/E26/ND 4/1PF	-20 °C to 45 °C
929002333693	8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF	-20 to +45 °C
929001997805	8W (60W) E26 Red Bulb	-20 to +45 °C
929001937253	4A19/PER/YELLOW/G/E26/ND 4/1PF	-20 °C to 45 °C
929001998105	8W (60W) E26 Yellow Bulb	-20 to +45 °C
929001997905	8W (60W) E26 Green Bulb	-20 to +45 °C
929001937453	4A19/PER/GREEN/G/E26/ND 4/1PF	-20 °C to 45 °C
929001937553	4A19/PER/PURPLE/G/E26/ND 4/1PF	-20 °C to 45 °C



# Specialty Lamps

