



# Built-in technology for additional features

## Specialty Lamps

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Benefits

- Party bulbs, the perfect festive touch for holidays and special occasions
- Dusk to dawn bulbs, is equipped with a built-in light sensor for added security
- 3-way bulbs, offers switching between 3 wattage settings to get exactly the right amount of light when you need it

### Features

- Long lifetime
- Excellent color consistency
- Dusk to Dawn
- Switching between 3 wattage settings

### Application

- Assisted Living
- Residential
- Hospitality

# Specialty Lamps

## Versions




8W (60W) E26 Blue Bulb - RFT



LEDbulb Color A19 E26 Red



LEDbulb A21 E26 FR



LEDbulb Color A19 E26 Orange




LEDbulb Color A19 E26 Blue



LEDbulb A19 E26 FR



8W (60W) E26 Red Bulb - RFT



LEDbulb Color A19 E26 Yellow




8W (60W) E26 Yellow Bulb - RFT



8W (60W) E26 Green Bulb - RFT




LEDbulb Color A19 E26 Green



LEDbulb Color A19 E26 Purple




## Dimensional drawing



| Product                                 | D       | C        |
|---|---------|----------|
| 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | 70.6 mm | 133.1 mm |

# Specialty Lamps

## Dimensional drawing



| Product                               | D       | C        |
|---------------------------------------|---------|----------|
| 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF | 61.5 mm | 109.8 mm |

| Product                  | D     | C      |
|--------------------------|-------|--------|
| 8W (60W) E26 Blue Bulb   | 60 mm | 107 mm |
| 8W (60W) E26 Green Bulb  | 60 mm | 107 mm |
| 8W (60W) E26 Red Bulb    | 60 mm | 107 mm |
| 8W (60W) E26 Yellow Bulb | 60 mm | 107 mm |

| Product                        | D     | C      |
|--------------------------------|-------|--------|
| 4A19/PER/BLUE/G/E26/ND 4/1PF   | 60 mm | 106 mm |
| 4A19/PER/GREEN/G/E26/ND 4/1PF  | 60 mm | 106 mm |
| 4A19/PER/ORANGE/G/E26/ND 4/1PF | 60 mm | 106 mm |
| 4A19/PER/PURPLE/G/E26/ND 4/1PF | 60 mm | 106 mm |
| 4A19/PER/RED/G/E26/ND 4/1PF    | 60 mm | 106 mm |
| 4A19/PER/YELLOW/G/E26/ND 4/1PF | 60 mm | 106 mm |

### Light Technical

LLMF At End Of Nominal Lifetime (Nom) 70 %

### Operating and Electrical

Input Frequency 60 Hz  
Starting Time (Nom) 0.5 s

### Controls and Dimming

Dimmable No

## General Information

## Specialty Lamps

| Order Code   | Full Product Name                       | Cap-Base | Rated            |                 |                  |
|--------------|---|----------|------------------|-----------------|------------------|
|              |   |          | Lifetime (Hours) | Switching Cycle | Nominal lifetime |
| 929001998005 | 8W (60W) E26 Blue Bulb                  | E26      | 10,950 hour(s)   | 20,000          | 10,950 hour(s)   |
| 929001937053 | 4A19/PER/RED/G/E26/ND 4/1PF             | E26      | 15,000 hour(s)   | 20,000          | 15,000 hour(s)   |
| 929002285133 | 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | E26D     | 15,000 hour(s)   | 50,000          | 15,000 hour(s)   |
| 929001937153 | 4A19/PER/ORANGE/G/E26/ND 4/1PF          | E26      | 15,000 hour(s)   | 20,000          | 15,000 hour(s)   |
| 929001937353 | 4A19/PER/BLUE/G/E26/ND 4/1PF            | E26      | 15,000 hour(s)   | 20,000          | 15,000 hour(s)   |
| 929002333693 | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF   | E26      | 15,000 hour(s)   | 50,000          | 15,000 hour(s)   |

| Order Code   | Full Product Name              | Cap-Base | Rated            |                 |                  |
|--------------|--------------------------------|----------|------------------|-----------------|------------------|
|              |                                |          | Lifetime (Hours) | Switching Cycle | Nominal lifetime |
| 929001997805 | 8W (60W) E26 Red Bulb          | E26      | 10,950 hour(s)   | 20,000          | 10,950 hour(s)   |
| 929001937253 | 4A19/PER/YELLOW/G/E26/ND 4/1PF | E26      | 15,000 hour(s)   | 20,000          | 15,000 hour(s)   |
| 929001998105 | 8W (60W) E26 Yellow Bulb       | E26      | 10,950 hour(s)   | 20,000          | 10,950 hour(s)   |
| 929001997905 | 8W (60W) E26 Green Bulb        | E26      | 10,950 hour(s)   | 20,000          | 10,950 hour(s)   |
| 929001937453 | 4A19/PER/GREEN/G/E26/ND 4/1PF  | E26      | 15,000 hour(s)   | 20,000          | 15,000 hour(s)   |
| 929001937553 | 4A19/PER/PURPLE/G/E26/ND 4/1PF | E26      | 15,000 hour(s)   | 20,000          | 15,000 hour(s)   |

### Light Technical

| Order Code   | Full Product Name                       | Beam Angle (Nom) | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Color Code | Luminous Flux |
|--------------|---|------------------|------------------------------------|-----------------------------|------------|---------------|
| 929001998005 | 8W (60W) E26 Blue Bulb                  | 120 degree(s)    | -                                  | -                           | -          | -             |
| 929001937053 | 4A19/PER/RED/G/E26/ND 4/1PF             | 330 degree(s)    | -                                  | -                           | Red        | -             |
| 929002285133 | 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | 250 degree(s)    | 2700 K                             | 90                          | 927        | 2,150 lm      |
| 929001937153 | 4A19/PER/ORANGE/G/E26/ND 4/1PF          | 330 degree(s)    | -                                  | -                           | Orange     | -             |
| 929001937353 | 4A19/PER/BLUE/G/E26/ND 4/1PF            | 330 degree(s)    | -                                  | -                           | Blue       | -             |
| 929002333693 | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF   | 220 degree(s)    | 2700 K                             | 90                          | 927        | 800 lm        |
| 929001997805 | 8W (60W) E26 Red Bulb                   | 120 degree(s)    | -                                  | -                           | -          | -             |
| 929001937253 | 4A19/PER/YELLOW/G/E26/ND 4/1PF          | 330 degree(s)    | -                                  | -                           | Yellow     | -             |
| 929001998105 | 8W (60W) E26 Yellow Bulb                | 160 degree(s)    | -                                  | -                           | -          | -             |
| 929001997905 | 8W (60W) E26 Green Bulb                 | 160 degree(s)    | -                                  | -                           | -          | -             |
| 929001937453 | 4A19/PER/GREEN/G/E26/ND 4/1PF           | 330 degree(s)    | -                                  | -                           | Green      | -             |
| 929001937553 | 4A19/PER/PURPLE/G/E26/ND 4/1PF          | 330 degree(s)    | -                                  | -                           | Purple     | -             |

### Operating and Electrical

| Order Code   | Full Product Name                       | Line Frequency | Power       |                    |
|--------------|---|----------------|-------------|--------------------|
|              |   |                | Consumption | Wattage Equivalent |
| 929001998005 | 8W (60W) E26 Blue Bulb                  | 60 Hz          | 8 W         | 40 W               |
| 929001937053 | 4A19/PER/RED/G/E26/ND 4/1PF             | 60 Hz          | 4 W         | 40 W               |
| 929002285133 | 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | -              | 18.5 W      | 150 W              |
| 929001937153 | 4A19/PER/ORANGE/G/E26/ND 4/1PF          | 60 Hz          | 4 W         | 40 W               |

| Order Code   | Full Product Name                     | Line Frequency | Power       |                    |
|--------------|---------------------------------------|----------------|-------------|--------------------|
|              |                                       |                | Consumption | Wattage Equivalent |
| 929001937353 | 4A19/PER/BLUE/G/E26/ND 4/1PF          | 60 Hz          | 4 W         | 40 W               |
| 929002333693 | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF | 60 Hz          | 8.8 W       | 60 W               |
| 929001997805 | 8W (60W) E26 Red Bulb                 | 60 Hz          | 8 W         | 40 W               |
| 929001937253 | 4A19/PER/YELLOW/G/E26/ND 4/1PF        | 60 Hz          | 4 W         | 40 W               |

## Specialty Lamps

| Order Code   | Full Product Name                    | Line      | Power       | Wattage    |
|--------------|--------------------------------------|-----------|-------------|------------|
|              |                                      | Frequency | Consumption | Equivalent |
| 929001998105 | 8W (60W) E26 Yellow Bulb             | 60 Hz     | 8 W         | 40 W       |
| 929001997905 | 8W (60W) E26 Green Bulb              | 60 Hz     | 8 W         | 40 W       |
| 929001937453 | 4A19/PER/<br>GREEN/G/E26/ND<br>4/1PF | 60 Hz     | 4 W         | 40 W       |

| Order Code   | Full Product Name                     | Line      | Power       | Wattage    |
|--------------|---------------------------------------|-----------|-------------|------------|
|              |                                       | Frequency | Consumption | Equivalent |
| 929001937553 | 4A19/PER/<br>PURPLE/G/E26/ND<br>4/1PF | 60 Hz     | 4 W         | 40 W       |

### Temperature

| Order Code   | Full Product Name                       | T-Case Maximum (Nom) |
|--------------|---|----------------------|
| 929001998005 | 8W (60W) E26 Blue Bulb                  | 80 °C                |
| 929001937053 | 4A19/PER/RED/G/E26/ND 4/1PF             | 125 °C               |
| 929002285133 | 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | 95 °C                |
| 929001937153 | 4A19/PER/ORANGE/G/E26/ND 4/1PF          | 125 °C               |
| 929001937353 | 4A19/PER/BLUE/G/E26/ND 4/1PF            | 125 °C               |
| 929002333693 | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF   | 95 °C                |

| Order Code   | Full Product Name              | T-Case Maximum (Nom) |
|--------------|--------------------------------|----------------------|
| 929001997805 | 8W (60W) E26 Red Bulb          | 80 °C                |
| 929001937253 | 4A19/PER/YELLOW/G/E26/ND 4/1PF | 125 °C               |
| 929001998105 | 8W (60W) E26 Yellow Bulb       | 80 °C                |
| 929001997905 | 8W (60W) E26 Green Bulb        | 80 °C                |
| 929001937453 | 4A19/PER/GREEN/G/E26/ND 4/1PF  | 125 °C               |
| 929001937553 | 4A19/PER/PURPLE/G/E26/ND 4/1PF | 125 °C               |


### Mechanical and Housing

| Order Code   | Full Product Name                       | Bulb Finish | Bulb Shape |
|--------------|---|-------------|------------|
| 929001998005 | 8W (60W) E26 Blue Bulb                  | Frosted     | A19        |
| 929001937053 | 4A19/PER/RED/G/E26/ND 4/1PF             | Red         | A19        |
| 929002285133 | 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | Frosted     | A21        |
| 929001937153 | 4A19/PER/ORANGE/G/E26/ND 4/1PF          | Orange      | A19        |
| 929001937353 | 4A19/PER/BLUE/G/E26/ND 4/1PF            | Blue        | A19        |
| 929002333693 | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF   | Frosted     | A19        |

| Order Code   | Full Product Name              | Bulb Finish | Bulb Shape |
|--------------|--------------------------------|-------------|------------|
| 929001997805 | 8W (60W) E26 Red Bulb          | Frosted     | A19        |
| 929001937253 | 4A19/PER/YELLOW/G/E26/ND 4/1PF | Yellow      | A19        |
| 929001998105 | 8W (60W) E26 Yellow Bulb       | Frosted     | A19        |
| 929001997905 | 8W (60W) E26 Green Bulb        | Frosted     | A19        |
| 929001937453 | 4A19/PER/GREEN/G/E26/ND 4/1PF  | Green       | A19        |
| 929001937553 | 4A19/PER/PURPLE/G/E26/ND 4/1PF | Purple      | A19        |

### Approval and Application

| Order Code   | Full Product Name                       | Ambient temperature range |
|--------------|---|---------------------------|
| 929001998005 | 8W (60W) E26 Blue Bulb                  | -20 to +45 °C             |
| 929001937053 | 4A19/PER/RED/G/E26/ND 4/1PF             | -20 °C to 45 °C           |
| 929002285133 | 18.5A21/PER/927/FR/P/E26/3WAY/T20 4/1PF | -20 to +45 °C             |
| 929001937153 | 4A19/PER/ORANGE/G/E26/ND 4/1PF          | -20 °C to 45 °C           |
| 929001937353 | 4A19/PER/BLUE/G/E26/ND 4/1PF            | -20 °C to 45 °C           |
| 929002333693 | 8.8A19/PER/927/FR/P/E26/D2D/T20 4/1PF   | -20 to +45 °C             |
| 929001997805 | 8W (60W) E26 Red Bulb                   | -20 to +45 °C             |
| 929001937253 | 4A19/PER/YELLOW/G/E26/ND 4/1PF          | -20 °C to 45 °C           |
| 929001998105 | 8W (60W) E26 Yellow Bulb                | -20 to +45 °C             |
| 929001997905 | 8W (60W) E26 Green Bulb                 | -20 to +45 °C             |
| 929001937453 | 4A19/PER/GREEN/G/E26/ND 4/1PF           | -20 °C to 45 °C           |
| 929001937553 | 4A19/PER/PURPLE/G/E26/ND 4/1PF          | -20 °C to 45 °C           |



# Specialty Lamps

