



Uni Posttop: Urban street light targets at residential areas, pathways, plazas, etc.

Uni Posttop

The modern shaped post top attracts customers' attention with its unique, streamlined design. The fixture distributes soft and homogeneous light to pathways, residential areas thanks to the application of the reflector. Various quality test based on Philips standards offers robustness not only to its design but also functionality, delivering table and outstanding performance to customers.

Benefits

- Modern streamlined design fits various application scenarios, i.e., residential areas, pathways, plazas.
- Robust design ensures both appearance classy and quality stability.
- Soft lighting due to the application of alumina reflector.

Features


- Excellent thermal management
- Optimized optics for efficient and comfortable lighting levels
- Injection die-casting aluminum body
- High- quality PC diffuser

Uni Posttop

Application

- Road and Street
- Parks and Plazas
- Residential
- Main urban roads and streets, side and residential roads and streets
- City centers and historical areas
- Cycle and pedestrian paths, squares, parks and playgrounds

Dimensional drawing



General Information

Driver included Yes

Light Technical

Color rendering index (CRI) 70

Controls and Dimming

Dimmable No

Mechanical and Housing

Optical cover type Polycarbonate
bowl/cover clear

Housing Color Gray

Mech. impact protection code IK08

Ingress protection code IP65

Approval and Application

CE mark Yes

Light Technical

Order Code	Full Product Name	Light source color	Correlated Color		Luminous Flux
			Temperature (Nom)		
911401696308	BDS400 LED WW 220V 30W WB PSU 7012	730 warm white	3000 K		3,900 lm
911401696408	BDS400 LED WW 220V 60W WB PSU 7012	730 warm white	3000 K		7,800 lm
911401696508	BDS400 LED NW 220V 30W WB PSU 7012	740 neutral white	4000 K		4,200 lm
911401696608	BDS400 LED NW 220V 60W WB PSU 7012	740 neutral white	4000 K		8,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401696308	BDS400 LED WW 220V 30W WB PSU 7012	30 W
911401696408	BDS400 LED WW 220V 60W WB PSU 7012	60 W

Order Code	Full Product Name	Power Consumption
911401696508	BDS400 LED NW 220V 30W WB PSU 7012	30 W
911401696608	BDS400 LED NW 220V 60W WB PSU 7012	60 W

