

Uni Wall Sconce

10575312



Uni Wall Mount Sconce: Urban up and down lighting
Wall Mounts applies on surface, e.g., parking garages, entrances, outdoor terrace and wall in garden.

Public areas all seek for the most reliable and professional lighting solutions, e.g., parking areas, entrances, outdoor terrace, and wall in garden. The Philips Uni Wall Mount Sconce can be installed easily in accordance with per scenario, delivering the optimized lighting to surroundings. The modern sleek design makes the fixture suitable to be installed either in renovation or new installation scenarios. The Philips Uni Wall Mount sconce helps you achieve superb reliability and more. Same as other product range in Philips, the product is designed under a variety of Philips quality standard with a good price/quality ratio. Therefore, Philips Uni Wall Mount Sconce offers another affordable, energy – efficient and stable choice in the existing wall Mounting family.

Benefits

- Modern streamlined design.
- Multiple mounting option.
- Easy directly mounted over a bracket.

Applications

- Walkways
- Parks and Plazas
- Outdoor Parking areas

Versions




Uni Wall Sconce




Uni Wall Sconce

Dimensional drawing



BWP411 LED NW 220V 40W WB PSU 7012



BWP410 LED NW 220V 40W WB PSU 7012

General Information

Driver included Yes

Light Technical

Color rendering index (CRI) 70

Operating and Electrical

Power Consumption 40 W

Controls and Dimming

Dimmable No

Mechanical and Housing

Housing Color Gray

Ingress protection code IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK08 [5 J vandal-protected]

Optical cover type Flat glass

Approval and Application

CE mark Yes

Light Technical

Order Code	Full Product Name	Luminous Flux	Correlated Color Temperature (Nom)	Light source color
61088399	BWP411 LED WW 220V 40W NB PSU 7012	5,000 lm	3000 K	730 warm white
61089099	BWP411 LED WW 220V 40W MB PSU 7012	5,000 lm	3000 K	730 warm white
61091399	BWP411 LED WW 220V 40W WB PSU 7012	5,000 lm	3000 K	730 warm white
61092099	BWP411 LED NW 220V 40W NB PSU 7012	5,400 lm	4000 K	740 neutral white
61093799	BWP411 LED NW 220V 40W MB PSU 7012	5,400 lm	4000 K	740 neutral white
61094499	BWP411 LED NW 220V 40W WB PSU 7012	5,400 lm	4000 K	740 neutral white
61082199	BWP410 LED WW 220V 40W NB PSU 7012	5,000 lm	3000 K	730 warm white
61083899	BWP410 LED WW 220V 40W MB PSU 7012	5,000 lm	3000 K	730 warm white
61084599	BWP410 LED WW 220V 40W WB PSU 7012	5,000 lm	3000 K	730 warm white
61085299	BWP410 LED NW 220V 40W NB PSU 7012	5,400 lm	4000 K	740 neutral white
61086999	BWP410 LED NW 220V 40W MB PSU 7012	5,400 lm	4000 K	740 neutral white
61087699	BWP410 LED NW 220V 40W WB PSU 7012	5,400 lm	4000 K	740 neutral white